


## PNP Silicon Switching Transistors

- High DC current gain: 0.1mA to 500 mA
- Low collector-emitter saturation voltage
- Complementary types: BSS79, BSS81 (NPN)



Type	Marking	Pin Configuration			Package
BSS80B	CHs	1 = B	2 = E	3 = C	SOT23
BSS80C	CJs	1 = B	2 = E	3 = C	SOT23
BSS82B	CLs	1 = B	2 = E	3 = C	SOT23
BSS82C	CMs	1 = B	2 = E	3 = C	SOT23

## Maximum Ratings

Parameter	Symbol	BSS80	BSS82	Unit
Collector-emitter voltage	$V_{CEO}$	40	60	V
Collector-base voltage	$V_{CBO}$	60		V
Emitter-base voltage	$V_{EBO}$	5		
DC collector current	$I_C$	800		mA
Peak collector current	$I_{CM}$	1		A
Base current	$I_B$	100		mA
Peak base current	$I_{BM}$	200		
Total power dissipation, $T_S = 77^\circ\text{C}$	$P_{tot}$	330		mW
Junction temperature	$T_j$	150		$^\circ\text{C}$
Storage temperature	$T_{stg}$	-65 ... 150		

## Thermal Resistance

Junction - soldering point <sup>1)</sup>	$R_{thJS}$	$\leq 220$	K/W
--	------------	------------	-----

<sup>1</sup>For calculation of  $R_{thJA}$  please refer to Application Note Thermal Resistance

**Electrical Characteristics** at  $T_A = 25^\circ\text{C}$ , unless otherwise specified.

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
<b>DC Characteristics</b>					
Collector-emitter breakdown voltage $I_C = 10 \text{ mA}, I_B = 0$	$V_{(\text{BR})\text{CEO}}$	40	-	-	V
		60	-	-	
Collector-base breakdown voltage $I_C = 10 \mu\text{A}, I_E = 0$	$V_{(\text{BR})\text{CBO}}$	60	-	-	
Emitter-base breakdown voltage $I_E = 10 \mu\text{A}, I_C = 0$	$V_{(\text{BR})\text{EBO}}$	5	-	-	
Collector cutoff current $V_{CB} = 50 \text{ V}, I_E = 0$	$I_{\text{CBO}}$	-	-	10	nA
Collector cutoff current $V_{CB} = 50 \text{ V}, I_E = 0, T_A = 150^\circ\text{C}$	$I_{\text{CBO}}$	-	-	10	$\mu\text{A}$
Emitter cutoff current $V_{EB} = 3 \text{ V}, I_C = 0$	$I_{\text{EBO}}$	-	-	10	nA
DC current gain 1) $I_C = 100 \mu\text{A}, V_{CE} = 10 \text{ V}$	$h_{\text{FE}}$	40	-	-	-
		75	-	-	
		40	-	-	
		100	-	-	
		40	-	-	
		100	-	-	
		40	-	120	
		100	-	300	
		40	-	-	
		50	-	-	
Collector-emitter saturation voltage1) $I_C = 150 \text{ mA}, I_B = 15 \text{ mA}$	$V_{\text{CEsat}}$	-	-	0.4	V
$I_C = 500 \text{ mA}, I_B = 50 \text{ mA}$		-	-	1.6	
Base-emitter saturation voltage 1) $I_C = 150 \text{ mA}, I_B = 15 \text{ mA}$	$V_{\text{BEsat}}$	-	-	1.3	
$I_C = 500 \text{ mA}, I_B = 50 \text{ mA}$		-	-	2.6	


1) Pulse test:  $t \leq 300 \mu\text{s}, D = 2\%$

**Electrical Characteristics** at  $T_A = 25^\circ\text{C}$ , unless otherwise specified.


Parameter	Symbol	Values			Unit
		min.	typ.	max.	
<b>AC Characteristics</b>					
Transition frequency $I_C = 20 \text{ mA}, V_{CE} = 20 \text{ V}, f = 100 \text{ MHz}$	$f_T$	-	250	-	MHz
Collector-base capacitance $V_{CB} = 10 \text{ V}, f = 1 \text{ MHz}$	$C_{cb}$	-	6	-	pF
Delay time $V_{CC} = 30 \text{ V}, I_C = 150 \text{ mA}, I_{B1} = 15 \text{ mA}, V_{BE(\text{off})} = 0.5 \text{ V}$	$t_d$	-	-	10	ns
Rise time $V_{CC} = 30 \text{ V}, I_C = 150 \text{ mA}, I_{B1} = 15 \text{ mA}, V_{BE(\text{off})} = 0.5 \text{ V}$	$t_r$	-	-	40	
Storage time $V_{CC} = 30 \text{ V}, I_C = 150 \text{ mA}, I_{B1}=I_{B2} = 15 \text{ mA}$	$t_{sig}$	-	-	80	
Fall time $V_{CC} = 30 \text{ V}, I_C = 150 \text{ mA}, I_{B1}=I_{B2} = 15 \text{ mA}$	$t_f$	-	-	30	

## Test circuits


### Delay and rise time




### Storage and fall time



**Total power dissipation**  $P_{\text{tot}} = f(T_S)$




**Collector-base capacitance**  $C_{\text{CB}} = f(V_{\text{CB}})$   
 $f = 1\text{MHz}$




**Permissible pulse load**

$P_{\text{totmax}} / P_{\text{totDC}} = f(t_p)$




**Transition frequency**  $f_T = f(I_C)$


$V_{\text{CE}} = 20\text{V}$




**Saturation voltage**  $I_C = f(V_{BEsat}, V_{CEsat})$   
 $h_{FE} = 10$




**Storage time**  $t_{stg} = f(I_C)$



**Delay time**  $t_d = f(I_C)$   
**Rise time**  $t_r = f(I_C)$




**Fall time**  $t_f = f(I_C)$




**DC current gain**  $h_{FE} = f(I_C)$


$V_{CE} = 10V$




### Package Outline



### Foot Print




### Marking Layout



### Packing

Code E6327: Reel ø180 mm = 3.000 Pieces/Reel

Code E6433: Reel ø330 mm = 10.000 Pieces/Reel



---

Published by Infineon Technologies AG,  
St.-Martin-Strasse 53,  
81669 München  
© Infineon Technologies AG 2005.  
All Rights Reserved.

### **Attention please!**

The information herein is given to describe certain components and shall not be considered as a guarantee of characteristics.  
Terms of delivery and rights to technical change reserved.  
We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

### **Information**

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office ([www.Infineon.com](http://www.Infineon.com)).

### **Warnings**

Due to technical requirements components may contain dangerous substances.  
For information on the types in question please contact your nearest Infineon Technologies Office.  
Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system.  
Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.