

T-35-19

HARRIS SEMICONDUCTOR

56E D

4302271 0040719 443 HAS


# High-Current, Silicon N-P-N VERSAWATT Transistors

Switching Applications

**Features:**

- Fast switching speed at temperatures up to 125°C
- Low  $V_{CE(sat)}$
- VERSAWATT plastic package

TERMINAL DESIGNATIONS



JEDEC TO-220AB

RCA-BUW64A, BUW64B, and BUW64C are epitaxial-base silicon n-p-n power transistors which feature fast switching speeds, low saturation voltages, and high safe-operating-area (SOA) ratings. They are specially designed for converters, inverters, pulse-width-modulated regulators and a variety of power switching circuits.

The BUW64A, BUW64B, and BUW64C transistors are supplied in the JEDEC TO-220AB (RCA VERSAWATT) plastic packages.

POWER TRANSISTORS

**MAXIMUM RATINGS, Absolute-Maximum Values:**

	BUW64A	BUW64B	BUW64C	
$V_{CEV}$				V
$V_{BE} = -1.5$ V .....	140	160	180	V
$V_{CEO}$ .....	90	110	130	V
$V_{EBO}$ .....		7		V
$I_{C(sat)}$ .....	5	5	4	A
$I_C$ .....		7		A
$I_{CM}$ .....		10		A
$I_B$ .....		5		A
$P_T$				W
$T_C$ up to 25°C .....		50		W/°C
$T_C$ above 25°C .....		0.4		Derate Linearly
$T_{emp}, T_J$ .....		-65 to 150		°C
$T_L$				°C
At distance $\geq 1/8$ in. (3.16 mm) from seating plane for 10 s max. ...		235		

ELECTRICAL CHARACTERISTICS, at Case Temperature  $T_C = 25^\circ\text{C}$  Unless Otherwise Specified

T-35-19

CHARACTERISTIC	TEST CONDITIONS				LIMITS						UNITS
	VOLTAGE V dc		CURRENT A dc		BUW64A		BUW64B		BUW64C		
	$V_{CE}$	$V_{BE}$	$I_C$	$I_B$	Min.	Max.	Min.	Max.	Min.	Max.	
$I_{CEV}$	140	-1.5			-	100	-	-	-	-	$\mu\text{A}$
	160	-1.5			-	-	-	100	-	-	
	180	-1.5			-	-	-	-	100	-	
$T_C = 125^\circ\text{C}$	140	-1.5			-	1	-	-	-	-	mA
	160	-1.5			-	-	-	1	-	-	
	180	-1.5			-	-	-	-	-	1	
$I_{EBO}$		-7	0		-	100	-	100	-	100	$\mu\text{A}$
$V_{CEO(sus)b}$			0.01 <sup>a</sup>	0	90	-	110	-	130	-	V
$h_{FE}$	2		0.2 <sup>a</sup>		30	-	30	-	30	-	
	2		4 <sup>a</sup>		-	-	-	-	20	-	
	2		5 <sup>a</sup>		20	-	20	-	-	-	
$V_{BE(sat)}$			4 <sup>a</sup>	0.4	-	-	-	-	-	1.4	V
			5 <sup>a</sup>	0.5	-	1.5	-	1.5	-	-	
$V_{CE(sat)}$			4 <sup>a</sup>	0.4	-	-	-	-	-	0.7	V
			5 <sup>a</sup>	0.5	-	0.8	-	0.8	-	-	
			7 <sup>a</sup>	0.7	-	1.5	-	1.5	-	1.5	
$I_S/b$	20		2.5		1	-	1	-	1	-	s
$ h_{fe} $ f = 5 MHz	10		0.5		10	40	10	40	10	40	
$f_T$	10		0.5		50	200	50	200	50	200	MHz
$C_{obo}$ f = 0.1 MHz	10 <sup>c</sup>				50	150	50	150	50	150	pF
$t_d^d$		-4	4	0.4	-	-	-	-	-	0.1	$\mu\text{s}$
			5	0.5	-	0.1	-	0.1	-	-	
$t_r^d$		-4	4	0.4	-	-	-	-	-	0.25	
			5	0.5	-	0.25	-	0.25	-	-	
$t_s^d$		-4	4	0.4 <sup>e</sup>	-	-	-	-	-	1	
			5	0.5 <sup>e</sup>	-	1	-	1	-	-	
$t_f^d$		-4	4	0.4 <sup>e</sup>	-	-	-	-	-	0.5	
			5	0.5 <sup>e</sup>	-	0.5	-	0.5	-	-	
$R_{\theta JC}$	4		5		-	2.5	-	2.5	-	2.5	$^\circ\text{C/W}$

<sup>a</sup> Pulsed: pulse duration = 300  $\mu\text{s}$ , duty factor  $\leq 2\%$ .

<sup>b</sup> CAUTION: The sustaining voltage  $V_{CEO(sus)}$  MUST NOT be measured on a curve tracer.

<sup>c</sup>  $V_{CB}$  value.

<sup>d</sup>  $V_{CC} = 70\text{ V}$ ,  $t_p = 20\ \mu\text{s}$

<sup>e</sup>  $I_{B1} = -I_{B2}$ .

HARRIS SEMICOND SECTOR

T-35-19




Fig. 1 - Maximum operating areas for all types ( $T_C = 25^\circ C$ ).

HARRIS SEMICOND SECTOR

POWER TRANSISTORS




Fig. 2 - Maximum operating areas for all types ( $T_C = 100^\circ C$ ).




Fig. 3 - Dissipation and  $I_{S/b}$  derating curves for all types.




Fig. 4 - Typical thermal-response characteristic for all types.

HARRIS SEMICOND SECTOR




Fig. 5 - Typical dc beta characteristics for all types.




Fig. 6 - Typical collector-to-emitter saturation voltage characteristics for all types.




Fig. 7 - Typical base-to-emitter saturation voltage characteristic for all types.




Fig. 8 - Typical small-signal forward-current transfer ratio characteristic for all types ( $f = 5 \text{ MHz}$ ).




Fig. 9 - Typical output characteristics for all types.




Fig. 10 - Typical saturated-switching-time characteristics as a function of collector current for all types ( $T_C = 25^\circ C$ ).




Fig. 11 - Typical saturated-switching-time characteristics as a function of collector current for all types ( $T_C = 125^\circ C$ ).




Fig. 12 - Typical common-base input ( $C_{ibo}$ ) or output ( $C_{obo}$ ) capacitance characteristic for all types.





Fig. 13 - Circuit for measuring switching times.

POWER TRANSISTORS

T-35-19



92CS-30381R1  
 $t_d = A-B$      $t_f = X-Y$   
 $t_r = B-C$      $t_f = Y-Z$   
 $t_{transition} = X-W$   
**NOTE: TRANSITION TIME FROM 90%  $I_{B1}$  TO 90%  $I_{B2}$  MUST BE LESS THAN 0.5  $\mu s$ .**

Fig. 14 - Phase relationship between input and output currents showing reference points for specification of switching times.

HARRIS SEMICONDUCTOR