


Central Semiconductor Corp.

Central Semiconductor Corp.

Central Semiconductor Corp.

Central Semiconductor Corp.

145 Adams Avenue
Hauppauge, New York 11788



2N5632 2N5633 2N5634 NPN
2N6229 2N6230 2N6231 PNP

COMPLEMENTARY SILICON POWER
TRANSISTORS

JEDEC TO-3 CASE

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N5632, 2N6229 series types are complementary silicon power transistors manufactured by the epitaxial base process mounted in a hermetically sealed metal case designed for high power amplifier and switching applications where high voltages are required.

MAXIMUM RATINGS ($T_C=25^\circ\text{C}$ unless otherwise noted)

	SYMBOL	2N5632 2N6229	2N5633 2N6230	2N5634 2N6231	UNIT
Collector-Base Voltage	V_{CB0}	100	120	140	V
Collector-Emitter Voltage	V_{CE0}	100	120	140	V
Emitter-Base Voltage	V_{EB0}	7.0	7.0	7.0	V
Collector Current	I_C	10	10	10	A
Collector Current (Peak)	I_{CM}	15	15	15	A
Base Current	I_B	5.0	5.0	5.0	A
Power Dissipation	PD	150	150	150	W
Operating and Storage Junction Temperature	T_J, T_{STG}	-65 TO +200			$^\circ\text{C}$
Thermal Resistance	θ_{JC}	1.17			$^\circ\text{C}/\text{W}$

ELECTRICAL CHARACTERISTICS ($T_C=25^\circ\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	2N5632 2N6229		2N5633 2N6230		2N5634 2N6231		UNIT
		MIN	MAX	MIN	MAX	MIN	MAX	
I_{CB0}	$V_{CB}=\text{Rated } V_{CB0}$		1.0		1.0		1.0	mA
I_{CEV}	$V_{CE}=\text{Rated } V_{CB0}, V_{EB}(\text{OFF})=1.5\text{V}$		1.0		1.0		1.0	mA
I_{CEV}	$V_{CE}=\text{Rated } V_{CB0}, V_{EB}(\text{OFF})=1.5\text{V}, T_C=150^\circ\text{C}$		5.0		5.0		5.0	mA
I_{CE0}	$V_{CE}=\frac{1}{2} \text{ Rated } V_{CB0}$		1.0		1.0		1.0	mA
I_{EB0}	$V_{BE}=7.0\text{V}$		1.0		1.0		1.0	mA
BV_{CE0}	$I_C=200\text{mA}$	100		120		140		V
$V_{CE}(\text{SAT})$	$I_C=7.5\text{A}, I_B=0.75\text{A}$		1.0		1.0		1.0	V
$V_{CE}(\text{SAT})$	$I_C=10\text{A}, I_B=2.0\text{A}$		2.0		2.0		2.0	V
$V_{BE}(\text{SAT})$	$I_C=7.5\text{A}, I_B=0.75\text{A}$		2.0		2.0		2.0	V
$V_{BE}(\text{ON})$	$V_{CE}=2.0\text{V}, I_C=5.0\text{A}$		1.5		1.5		1.5	V
hFE	$V_{CE}=2.0\text{V}, I_C=5.0\text{A}$	25	100	20	80	15	60	
hFE	$V_{CE}=2.0\text{V}, I_C=10\text{A}$	5.0		5.0		5.0		
hfe	$V_{CE}=10\text{V}, I_C=2.0\text{A}, f=1.0\text{kHz}$	15		15		15		
f_T	$V_{CE}=20\text{V}, I_C=1.0\text{A}, f=0.5\text{MHz}$	1.0		1.0		1.0		MHz
C_{ob}	$V_{CB}=10\text{V}, I_E=0, f=0.1\text{MHz}$ (NPN types)		300		300		300	pF
C_{ob}	$V_{CB}=10\text{V}, I_E=0, f=0.1\text{MHz}$ (PNP types)		600		600		600	pF

CentralTM
Semiconductor Corp.

145 Adams Avenue
Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824
www.centrasemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix " TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix " PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms