

1350HV

High voltage fast-acting brick fuse



Product features

- 13 x 5.0 x 5.0 mm surface mount package
- · High voltage fast-acting brick fuse
- Up to 600 Vdc voltage rating
- · Ceramic tube, silver plated cap construction
- Moisture sensitivity level (MSL): 1

Applications

Primary and secondary circuit protection:

- Server & telecom systems, including 380 Vdc distribution
- · Single phase and 3-phase UPS
- 380 Vdc DC-DC converters
- High voltage DC-DC conversion
- · Power factor correction
- · Capacitor output protection

Environmental compliance






Agency information

cURus Recognition file number: E19180, Guide JDYX2



Ordering part number



Packaging prefix

TR- (1000 parts on a 13" diameter tape and reel)



Electrical characteristics

Amp Rating	% of rated current	Opening time
1 A ~ 7.5 A	100%	4 hours minimum
1 A ~ 7.5 A	200%	120 seconds maximum

Product specifications


Part number	Current rating (A)	Voltage (Vac)	rating (Vdc)	Interrupti @ rated vo (A) Vac		Typical resistance² (mΩ)	Typical voltage drop (mV)	Typical pre-arcing³ I²t (A²s)	Part marking
1350HV1-R	1	350	600	100	100	252	335	0.5	1
1350HV1-25-R	1.25	350	600	100	100	192	325	0.95	1.25
1350HV1-6-R	1.6	350	600	100	100	116	230	2.3	1.6
1350HV2-R	2	350	600	100	100	93	255	4.1	2
1350HV2-5-R	2.5	350	600	100	100	51	174	2.6	2.5
1350HV3-15-R	3.15	350	600	100	100	39	165	3.0	3.15
1350HV4-R	4	350	500	100	100	31	175	5.5	4
1350HV5-R	5	350	500	100	100	22	155	11.5	5
1350HV6-R	6	350	400	100	200	16.3	155	15	6
1350HV7-5-R	7.5	350	400	100	200	13.5	165	25	7.5


^{1.} AC Interrupting rating (measured at designated voltage, 100% power factor); DC Interrupting rating (measured at designated voltage, time constant of less than 50 microseconds, battery source)

3.Typical pre-arcing I2t are measured at 10 In current, DC battery bank

Dimensions- mm


Drawing not to scale





Rating	L	w	н
1 A ~ 7.5 A	13.20 ± 0.50	2.80 ± 0.50	5.05 ± 0.50

Recommended pad layout



Recommended trace thickness is 35 um; the minimum trace width is 5 mm Recommended stencil thickness is 0.15 mm

1350HV is also compatible with Littlefuse LF485 pad layout; wave solder pad size $5.6 \text{ mm} \times 6.9 \text{ mm}$ and reflow solder pad size $5.6 \text{ mm} \times 3.5 \text{ mm}$

General specifications

Operating temperature: -40 °C to +125 °C with proper derating factor applied

Thermal shock: MIL-STD-202,Method 107G -40 °C/+125 °C. Note: Number of cycles required 100 times

Mechanical shock: Figure 1 of Method 213. Condition C, 100 g, 6 ms

Mechanical vibration: MIL-STD-202G, Method 204, 5 g's for 20 minutes, 12 cycles each of 3 orientations. Test from 10-2000 Hz

Resistance to solder heat: MIL-STD-202G Method 210F, condition D (+260 °C,10 s)


Solderability test: J-STD-002, Method B1 Steam aging 1 hour, Solder temperature +255 ± 5 °C, solder immersion time 5 s

^{2.}DC Cold resistance are measured at <10% of rated current in ambient temperature of +25 $^{\circ}\text{C}$

1350HV High voltage fast-acting brick fuse


Packaging information - mm


1000 parts per 13" diameter reel (EIA-481 compliant) Drawing not to scale



Dimension	millimeter
W	24.00
F	11.50
E1	1.75
E2	N/A
P0	4.00
P1	8.00
P2	2.00
DO	1.50
D1	1.50
A0	4.85
В0	12.75
КО	4.90
T	0.40


Reel dimension- mm






Dimension	millimeter
A	330 ± 1
В	2.5 ± 0.2
С	13.5 ± 0.2
D	N/A
N	100 ± 0.5
W1	24.8 ± -0.5
W2	30.4 max
W3	N/A

Temperature derating curve



Current vs. time curve



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm3 <350	Volume mm3 ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm³ <350	Volume mm³ 350 - 2000	Volume mm³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

100 °C	150 °C
150 °C	200 °C
60-120 seconds	60-120 seconds
3 °C/ second max.	3 °C/ second max.
183 °C 60-150 seconds	217 °C 60-150 seconds
Table 1	Table 2
20 seconds*	30 seconds*
6 °C/ second max.	6 °C/ second max.
6 minutes max.	8 minutes max.
	150 °C 60-120 seconds 3 °C/ second max. 183 °C 60-150 seconds Table 1 20 seconds* 6 °C/ second max.

^{*} Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard

1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com/electronics

© 2022 Eaton All Rights Reserved Printed in USA Publication No. ELX1041 BU-ELX22099 August 2022

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

