



Product description

Eaton's Bussmann® series British Standard fuse holders are specifically designed to fit British standard fuse links.



Catalogue symbol for Camaster range

· CM(amp)F: Front connected

· CM(amp)FC: Front connected compact

Agency information:

· ASTA Certified to BS88-1 and IEC 60269-1

Technical data:

Rated voltage: 690 V a.c.Rated current: 20 to 100 A

Packaging:

20 to 63 A: 10 per pack100 A: 5 per pack

Table 1. Part numbers details

Fuse holder description	Colour	20 A	32 A	63 A	100 A
Front connected	Black	CM20F	CM32F*	CM63F*	CM100F*
	Green		CM32FG*		
	White		CM32FW*	CM63FW*	CM100FW*
Front connected	Black		CM32FC		
compact	Green		CM32FCG		
	White		CM32FCW		

^{*} Back studs can be retrofitted as standard

Table 2. Technical data

Part numbers	Rated current (Amps)	Rated voltage (V a.c.)	Agency markings	Minimum conductor size	Maximum conductor size	Suggested terminal torque values	Compatible fuse links	Packaging
CM20F	20	690	ASTA certified	0.5 mm ²	16 mm ²	2 to 2.5 Nm	NITD, NIT	10
CM32FC	32		to BS88-1 and IEC 60269-1	0.5 mm ²	16 mm ²	2 to 2.5 Nm	NITD, NIT	10
CM32F	32			1.5 mm ²	16 mm ²	2 to 2.5 Nm	AAO, TIA	10
CM63F	63			1.5 mm ²	70 mm ²	3 to 3.5 Nm	BAO, TIS	10
CM100F	100			1.5 mm ²	70 mm ²	3 to 3.5 Nm	OSD	5

Weights:


CM20F: 130 gramsCM32FC: 130 gramsCM32F: 158 gramsCM63F: 210 gramsCM100F: 207 grams


Table 3. Accessories


Catalogue numbers	Description	Pack quantity
32BSC	Back stud for 20-32 A Compact Camaster	10
32BS	Back stud conversion kit for 32 A Camaster	10
63-100BS	Back stud for 63-100 A Camaster	5
32CMLC	Neutral link for 32 A Compact Camaster	10
32CML	Neutral link for 32 A Camaster	1
63-100CML	Neutral link for 63-100 A Camaster	1
32LSCC	Lockable safety carrier 20-32 A Compact	3
32LSC	Lockable safety carrier 32 A	3
63-100LSC	Lockable safety carrier 63-100 A	3




Dimensions - mm












CM20F and CM32FC

Dimensions - mm












CM32F











CM63F

Dimensions - mm









CM100F

Catalogue symbol for Safeloc

· See table below

Agency information:

· ASTA Certified to IEC 60269

Technical data:

Rated voltage: 550 V a.c.Rated current: 32 to 63 A

Packaging:

32 A: 10 per pack63 A: 5 per pack

Table 4. Part numbers details

Fuse holder description	Colour	32 A	63 A	
Back stud/back stud	Black	32NNSBS	63ENSBS	
	Green	32NNSBSGREEN		
	White	32NNSBSWHITE	63ENSBSWHITE	
Front connected/front connected	Black	32NNSF	63ENSF	
	Green	32NNSFGREEN		
	White	32NNSFWHITE	63ENSFWHITE	
Front connected/back stud	Black	32NNSFBS	63ENSFBS	
	White	32NNSFBSWHITE	63ENSFBSWHITE	


Table 5. Technical data


Rated current (Amps)	Rated voltage (V a.c.)	Agency markings	Minimum conductor size	Maximum conductor size	terminal torque values	Compatible fuse links	Packaging
32	550	ASTA certified to IEC 60269	0.5 mm ²	16 mm ²	2-2.5 Nm	NSD	10
63			1.5 mm ²	35 mm ²	3-3.5 Nm	ESD	5


Weights:

32NNSBS: 113 grams
32NNSF: 85 grams
32NNSFBS: 100 grams
63ENSBS: 255 grams
63ENSF: 175 grams
63ENSFBS: 215 grams

Dimensions - mm








32NNSFFront connected/front connected

Dimensions - mm



Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, and Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton Internet pages and Eaton order confirmations.

Eaton EMEA Headquarters Route de la Longeraie 7 1110 Morges, Switzerland

Eaton Electrical Products Limited Melton Road Burton-on-the-Wolds Leicestershire, LE12 5TH United Kingdom

© 2019 Eaton All Rights Reserved PDF Only Publication No. 10415 April 2019



Eaton is a registered trademark.

All other trademarks are property of their respective owners.