

 $C \in$

For use in:

Mil/Aero Test Stands
Packaging Equipment
Robotic Arms
Factory Automation Systems

LRS-18 Series

Spring-Loaded LVIT Linear Position Sensor

Long Lasting, Contactless, Inductive Sensors

The LRS-18 series of LVIT (Linear Variable Inductance Transducer) spring-loaded position sensors by Alliance Sensors Group are contactless devices designed for dimensional or position measuring applications in factory automation and in various industrial and commercial applications, such as: automotive testing, mil/aero test stands, robotic arms, and packaging equipment. An ideal solution for when the sensing element cannot be attached to the object being measured. LRS-18s are offered in full scale ranges from 0.5 to 4.0 inches (12.5 to 100 mm) with excellent resolution and high stroke-to-length ratios. Maximum tip force on the item being measured is 1 pound.

LRS-18 sensors have a 0.75 inch (19 mm) diameter aluminum or stainless steel body with an M18 x 1 thread and come with two hex jam nuts for easy installation in place of an 18 mm analog prox sensor. These sensors use a 0.25 inch diameter probe equipped with an AGD No. 9 contact tip, and are offered with either an axial cable or a connector. Operating from a variety of DC voltages. These sensors are available with a choice of four analog outputs and they all include ASG's proprietary SenSet™ field recalibration feature.

Features:

- Spring-loaded LVIT Technology™ (Linear Variable Inductance Transducer)
- Ranges from 0.5 to 4.0 inches (12.5 to 100 mm)
- Contactless operation prevents internal wearout from dithering or rapid cycling
- Excellent stroke-to-length ratio
- Proprietary SenSet[™] field adjustable range scaling

Specifications:

Analog I/Os: 0-5 V or 0.5-4.5 V output with 8 -30 V input, 35 mA max.

0-10 V DC output with 12-30 V input, 35 mA max.

4-20 mA (3-wire) output with 18-30 V input, 60 mA max (75 C max).

Measuring Ranges: 12.5-100 mm (0.5 to 4 inches) Full Scale (nominal)

Linearity Error: ± 0.15% of FSO typical, ± 0.25% of FSO max

Resolution: 0.025% of FSO

Operating Temperature: -20 to 85 C (-40 to 105 C extended temperature range)

Temperature Coefficient: ≤0.015% of FS/deg C

Vibration: 5-20 Hz, 0.5 inch p-p; 20-2000 Hz, 4.2 g p-p

Shock: 1000 g, 11 msec. Terminations: IEC IP-67

Humidity: 95% RH, non-condensing


ALLIANCE SENSORS GROUP

LRS-18 Series



Wiring Table							
I/O Function	Cable Color	M12 Pin	PT02-10 Pin				
+DC Power input	Red	1	Е				
Ground	Black	2	D				
Analog output	Green	3	Α				
Current output	Green	4	^				
SenSet™	White	5	В				

Unit Length Table						
Nominal Range 'A' Inches [mm]	Body Length "B" Inches [mm]	Spring Rate Lbf/in [kgf/cm]	Max. Force Lbf [kgf]			
0.5 [12.7]	3.50 [88.9]	0.75 [0.134]	0.9 [0.41]			
1.0 [25]	4.00 [101.6]	0.75 [0.134]	0.9 [0.41]			
2.0 [50]	5.08 [129.0]	0.43 [0.077]	1.0 [0.45]			
3.0 [75]	6.16 [156.5]	0.30 [0.054]	1.0 [0.45]			
4.0 [100]	7.25 [184.1]	0.23 [0.041]	1.0 [0.45]			



Ordering Information:

Series	Output Type	Housing Thread	Range, Metric	Termination Direction	Termination	Output	Housing Material
LRS	X-	XX-	XXX-	X-	XX-	XX-	X-
	E- Voltage	18 - M18	013 - 12.7 mm	A - Axial	00 - 1 m cable	05 - 0.5 to 4.5 VDC	A - Aluminum
	I- Current		025 - 25 mm		01 - 5-pin M12	06 - 4.5 to 0.5 VDC	S - 300 Series SS
			050 - 50 mm		02 6-pin PT02	10 - 0 to 10 VDC	
			075 - 75 mm		00 - 3 m cable	11 - 10 to 0 VDC	
			100 - 100 mm			20 - 4 to 20 mA	
						21 - 20 to 4 mA	
						50 - 0 to 5 VDC	
						51 - 5 to 0 VDC	

ALLIANCE SENSORS GROUP

Alliance Sensors Group 102 Commerce Drive, Unit 8 Moorestown, New Jersey 08057 USA Ph: 856-727-0250 www.alliancesensors.com info@alliancesensors.com