

Type FCD

Fast Acting High Breaking Capacity

5 x 20 mm Ceramic Fuse



www.optifuse.com (619) 593-5050

Agency Standards and Listings:



Meets IEC 60127 standards

Interrupt Ratings:

250mA ~ 16A 1,500A at 250V AC (All)

250mA ~ 16A 1,000A at 250V DC UL

FCD-6.3A-UL: 250mA ~ 6.3A 10,000A at 250V AC UL

*FCD-6.3A not UL approved at 10,000A at 250V AC UL

Time Characteristics

Rated Current	210%		275%		400%		1000%
	MAX	MIN	MAX	MIN	MAX	MAX	
250mA~4A	30 min	10 ms	2 sec	3 ms	300 ms	20 ms	
5A~6.3A	30 min	10 ms	3 sec	3 ms	300 ms	20 ms	
8A~10A	30 min	40 ms	20 sec	10 ms	1 sec	30 ms	
>10A	30 min	40 ms	20 sec	10 ms	1 sec	40 ms	

Operating Temperature:

-55°C to +125°C


Material:

- Ceramic Body/Nickel Plated Brass Caps
- Lead Wire Ø0.65mm Diameter – 8A and less.
- Ø0.8mm Diameter – 8a~ 12A.
- Ø1.0mm Diameter – over 12A.

Cartridge Part number	Axial Lead Part number	Amper e Rating	Nominal Melting I ² t A ² Sec	Voltage Rating								
				CCC	CQC	SEMKO	VDE	BSI	PSE	KC	CE	
FCD-200mA	FCD-P-200mA	200mA	0.0048	*	*	*	*	*	*	*	*	*
FCD-250mA	FCD-P-250mA	250mA	0.0040	*	*	*	*	*	*	*	*	*
FCD-315mA	FCD-P-315mA	315mA	0.0142	*	*	*	*	*	*	*	*	*
FCD-400mA	FCD-P-400mA	400mA	0.0200	*	*	*	*	*	*	*	*	*
FCD-500mA	FCD-P-500mA	500mA	0.0309	*	*	*	*	*	*	*	*	*
FCD-630mA	FCD-P-630mA	630mA	0.0672	*	*	*	*	*	*	*	*	*
FCD-800mA	FCD-P-800mA	800mA	0.1210	*	*	*	*	*	*	*	*	*
FCD-1A	FCD-P-1A	1A	0.2019	*	*	*	*	*	*	*	*	*
FCD-1.25A	FCD-P-1.25A	1.25A	0.4489	*	*	*	*	*	*	*	*	*
FCD-1.6A	FCD-P-1.6A	1.6A	1.243	*	*	*	*	*	*	*	*	*
FCD-2A	FCD-P-2A	2A	2.204	*	*	*	*	*	*	*	*	*
FCD-2.5A	FCD-P-2.5A	2.5A	1.995	*	*	*	*	*	*	*	*	*
FCD-3.15A	FCD-P-3.15A	3.15A	4.271	*	*	*	*	*	*	*	*	*
FCD-4A	FCD-P-4A	4A	12.22	*	*	*	*	*	*	*	*	*
FCD-5A	FCD-P-5A	5A	24.20	*	*	*	*	*	*	*	*	*
FCD-6.3A	FCD-P-6.3A	6.3A	51.30	*	*	*	*	*	*	*	*	*
FCD-8A	FCD-P-8A	8A	102.2	*	*	*	*	*	*	*	*	*
FCD-10A	FCD-P-10A	10A	204.7	*	*	*	*	*	*	*	*	*
FCD-12 A	FCD-P-12A	12A	360.5	*	*	*	*	*	*	*	*	*
FCD-12.5A	FCD-P-12.5A	12.5A	407.6	*	*	*	*	*	*	*	*	*
FCD-15A	FCD-P-15A	15A	602.5	*	*	*	*	*	*	*	*	*
FCD-16A	FCD-P-16A	16A	642.7	*	*	*	*	*	*	*	*	*

250V

Mechanical Dimensions: Inches [mm]




Note: All specifications subject to change without notice.


Type FCD
Fast Acting High Breaking Capacity
5 x 20 mm Ceramic Fuse



www.optifuse.com (619) 593-5050

Part Number FCD
TIME CURRENT CURVES



<p>Warning:</p> 	<ul style="list-style-type: none"> -Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame. -Glass Fuse device are intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated. -Avoid contact of Glass Fuse device with chemical solvent. Prolonged contact will damage the device performance.
--	---

Note: All specifications subject to change without notice.