EMC Components

Common mode filters Automotive power line (for power train/safety) **ACM-V** series








FEATURES

- Exclusive square type closed magnetic core designed as an exclusive core is used, so it can be small while maintaining the same features.
- OLow profile design makes it optimal for surface mounting.
- Excellent impedance characteristics, making it great for suppressing common mode noise.
- Olt can handle up to a maximum of 16A, including temperature derating.
- ○Covers a wide operating temperature range from –40 to +125°C.
- Operating temperature range: -40 to +125°C (Does not include self-heating.)
- Compliant with AEC-Q200

APPLICATION

OMeasures against common mode noise in power lines for various DC power lines, multimedia devices, and various electronic devices, including automotive power trains and safety applications.

PART NUMBER CONSTRUCTION




CHARACTERISTICS SPECIFICATION TABLE

| Common mode | e impedance | DC resistance | Rated current | | | Rated voltage | Insulation resistance | Part No. |
|-------------|-------------|---------------|-----------------------------------|---------|---------|---------------|-----------------------|---------------------|
| [at 100MHz] | | | Operating environment temperature | | | | | |
| | | | -40~85 ℃ | 105 ℃ | 125 °C | | | |
| (Ω)min. | (Ω)typ. | (mΩ)max. | (A)max. | (A)max. | (A)max. | (V)max. | (MΩ)min. | |
| 240 | 350 | 2.9 | 16.0 | 14.0 | 10.0 | 80 | 10 | ACM12V-351-2PL-TL00 |
| 500 | 700 | 6 | 13.0 | 11.0 | 8.0 | 80 | 10 | ACM12V-701-2PL-TL00 |
| 1200 | 1700 | 12 | 7.0 | 6.0 | 4.8 | 80 | 10 | ACM12V-172-2PL-TL00 |

* Please refer to the derating curve for the rated current.

Derating



Measurement equipment

| nologies |
|-----------|
| RPORATION |
| nologies |
| |




* Equivalent measurement equipment may be used.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (1/4)20240116

ACM12V type

IMPEDANCE VS. FREQUENCY CHARACTERISTICS




Measurement equipment

| Product No. | Manufacturer | | | |
|---|-----------------------|--|--|--|
| 4991B | Keysight Technologies | | | |
| * Equivalent measurement equipment may be used. | | | | |

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (2/4) 20240116


ACM12V type

SHAPE & DIMENSIONS




Dimensions in mm


RECOMMENDED LAND PATTERN




CIRCUIT DIAGRAM




RECOMMENDED REFLOW PROFILE







Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm





Dimensions in mm

PACKAGE QUANTITY

Package quantity 500 pcs/reel

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

| Operating | Storage | Individual | |
|---------------------|----------------------|------------|--|
| temperature range * | temperature range ** | weight | |
| –40 to +125 °C | –40 to +125 °C | 2.3 g | |

The operating temperature range of this product does not include selfheating. The product can be used up to 150°C including selfheating.

When using the product in an environment at 125°C, use the product within the current range shown in the table on page 1/4 of this catalog.

**The storage temperature range is for after the assembly.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

EMC Components

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products

REMINDERS

The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less).

If the storage period elapses, the soldering of the terminal electrodes may deteriorate.

- OD not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- Owhen embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Ocarefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
- Ouse a wrist band to discharge static electricity in your body through the grounding wire.
- Obo not expose the products to magnets or magnetic fields.
- Obo not use for a purpose outside of the contents regulated in the delivery specifications.

The products described in this catalog are intended to be installed in automobiles or automotive electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) and to be used in automobiles (including the case where the said automotive product is mounted in a vehicle) or standard applications as general electronic equipment in automotive applications or standard applications as general electronic equipment in automotive applications in accordance with the scope and conditions described in this specification, while the said automotive or general electronic equipment including the said product is intended to be used in the usual operation and usage methods, respectively. Other than automotive or automotive products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality requires a more stringent level of safety or reliability, or whose failure, malfunction or defect could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in this specification, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment

- (7) Transportation control equipment
- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.