ECMT1V20 Common mode choke, through-hole



Product features

- Closed magnetic path reduces conductive EMI emission
- High impedance and inductance values
- Robust construction
- · High voltage isolation
- Independent winding sections
- Rated voltage: 250 Vac

Applications

- Industrial IoT equipment
- Motion controls
- Power supplies
- Battery backup
- Renewable energy products
- Smart meters
- Solar/wind generators, inverters, charger controllers
- Medical equipment
- High tech consumer products
- Appliances

Environmental compliance and general specifications

- Storage temperature range (Component): -40 °C to +85 °C
- Operating temperature range: -40 °C to +125 °C (ambient plus self-temperature rise)
- Wave solder temperature: +260 °C maximum





Product specifications

Part number ⁷	OCL ¹ (mH) minimum (1-2), (4-3)	DCR ² (Ω) maximum (1-2), (4-3) @ +25 °C	I _{ms} ³ (A) (1-4) short 2,3	SRF (kHz) minimum	Hi-pot⁴ (Vac)	Hi-pot⁵ (Vac)	Insulation resistance ⁶ (MΩ) minimum
ECMT1V2023S-2R0-R	2.0	0.08	1.5	976	1500	1000	100
ECMT1V2017H-2R0-R	2.0	0.08	1.5	976	1500	1000	100
ECMT1V2023S-200-R	20	0.55	1.0	245	1500	1000	100
ECMT1V2017H-200-R	20	0.55	1.0	245	1500	1000	100
ECMT1V2023S-300-R	30	0.9	0.8	160	1500	1000	100
ECMT1V2017H-300-R	30	0.9	0.8	160	1500	1000	100
ECMT1V2023S-600-R	60	2.1	0.4	96	1500	1000	100
ECMT1V2017H-600-R	60	2.1	0.4	96	1500	1000	100

1. Open circuit inductance (OCL) Test parameters: 1 kHz, 0.25 Vrms, 0.0 Adc, +25 $^{\circ}\mathrm{C}$

2. DCR Test parameters: 4-wire method measured from the root of base, +25 $^{\circ}\mathrm{C}$

3. Imms: Maximum DC current for an approximate temperature rise of 40 °C without core loss. Derating is necessary for AC currents. PCB layout, trace thickness and width, air-flow, and proximity of other heat generating components will affect the temperature rise. It is recommended that the temperature of the part not exceed +125 °C under worst case operating conditions verified in the end application.

4. Hi-pot: Coil-Coil, 2 seconds, 5 mA

5. Hi-pot: Coil-Core, 2 seconds, 5 mA

6. Insulation Resistance: Coil-Coil and Coil-Core, at 500 Vdc 7. Part Number Definition: ECMT1Vxxxxy-zzz-R


ECMT1V = Product code


xxxx= Size indicator y= Orientation H= horizontal, S= vertical

zzz=Inductance value in mH, R= decimal point, If no R is present last digit indicates number of zeros -R= RoHS compliant


Mechanical parameters, schematic, pad layout (mm)

ECMT1V2023S-xxx-R






Recommended PCB layout




Recommended PCB layout


Schematic




Schematic





ECMT1V2017H-xxx-R















Part number	Α	В	С	D	E	F	G
ECMT1V2023S-xxx-R	17.5 max.	20.0 max.	23.0 max.	3.5 ± 0.5	10.0 ± 0.5	13.0 ± 0.5	0.7 ± 0.1
ECMT1V2017H-xxx-R	19.5 max.	19.5 max.	17.0 max.	3.5 ± 0.5	10.0 ± 0.5	13.0 ± 0.5	0.7 ± 0.1

Part marking: xxx-wwyy, xxx =inductance value in mH, wwyy= lot code Traces or vias underneath the inductor is not recommended


Technical Data **ELX1093** Effective September 2021

Packaging information (mm)

ECMT1V2023S-xxx-R Supplied in tray, 10 trays per carton. (81 parts per tray x 10 trays per box = 810 parts per carton) (Tray height 22 mm)




ECMT1V2017H-xxx-R Supplied in tray, 10 trays per carton. (99 parts per tray x 10 trays per box = 990 parts per carton) (Tray height 24 mm)



ECMT1V20 Common mode choke, through-hole


Impedance vs frequency



Measurement method




Common Mode




Differential Mode

Inductance vs frequency



ECMT1V20 Common mode choke, through-hole

Wave solder profile



Reference EN 61760-1:2006

Profile feature		Standard SnPb solder	Lead (Pb) free solder	
Preheat	• Temperature min. (T _{smin})	100 °C	100 °C	
	• Temperature typ. (T _{styp})	120 °C	120 °C	
	• Temperature max. (T _{smax})	130 °C	130 °C	
	• Time (T_{smin} to T_{smax}) (t_s)	70 seconds	70 seconds	
$\overline{\Delta}$ preheat to max Temperature		150 °C max.	150 °C max.	
Peak tempera	ature (T _P)*	235 °C – 260 °C	250 °C – 260 °C	
Time at peak temperature (t _p)		10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave	
Ramp-down r	ate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	
Time 25 °C to	0 25 ℃	4 minutes	4 minutes	

Manual solder

+350 °C, 4-5 seconds. (by soldering iron), generally manual, hand soldering is not recommended.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122 United States www.eaton.com/electronics

FATON Powering Business Worldwide © 2021 Eaton All Rights Reserved Printed in USA Publication No. ELX1093 BU-ELX21103 September 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

