

CCD DRIVER CMOS IC

The μPD16502 is a vertical drive interface for CCD area image sensor incorporating a level conversion circuit and three-level output function.

Using the CMOS process provides a low power consumption and a optimum transmission delay and low output ON resistance to drive the CCD image sensor.


FEATURES

- Low power consumption: 6.0 mA TYP.
- Low output ON resistance: 18 Ω TYP.
- High withstand voltage: 25 V MAX.
- Complete one-chip vertical drive interface circuit capable of connection with the clock generator (CMOS IC)
Middle level power V_{DD2a} and V_{DD2b} can be set with separate voltage.


ORDERING INFORMATION

Order name	Package
μPD16502GS	20-pin plastic SOP (300 mil)

BLOCK DIAGRAM



TERMINAL CONNECTION DIAGRAM (Top View)



ABSOLUTE MAXIMUM RATINGS ($T_a = 25\text{ }^\circ\text{C}$, GND = 0 V)

Power Withstand Voltage 1	$V_{DD1} - V_{SS}$	25	V
Power Withstand Voltage 2	$V_{DD2} - V_{SS}$	17	V
Power Withstand Voltage 3	$V_{CC} - GND$	7	V
Low Level Power Withstand Voltage	$V_{SS} - GND$	-10	V
Input Voltage	V_{IN}	-0.5 to $V_{CC} + 0.5$	V
I/O Clamp Diode Current	I_{IC}, I_{OC}	±10	mA
Maximum DC Load Current	I_{ODC}	±3	mA
Maximum Load Capacitance	C_L	30 000	pF/pin
Allowable Loss	P_D	200	mW
Storage Temperature	T_{stg}	-60 to +150	°C

Note: Use voltage $V_{DD2} < V_{CC}$

RECOMMENDED OPERATING CONDITIONS

(If no special specifications are stated grounding is 0 V, T_a ranges from -10 to $+60$ °C.)

CHARACTERISTICS	SYMBOL	RATING	UNIT
Voltage Across the Power 1 and Power 2 Supply	$V_{DD1} - V_{DD2}$	6.5 to 15.5	V
Voltage Across the Power 2 and Low Level Power Supply	$V_{DD2} - V_{SS}$	7.0 to 10.0	V
Power 2 Supply	V_{DD2}	0.0 to 4.0	V
Power 3 Supply	V_{CC}	4.75 to 5.25	V
High Level Input Voltage	V_{IH}^*	3.5 to V_{CC}	V
Low Level Input Voltage	V_{IL}^*	0.0 to 1.0	V
Operating Temperature	T_{opt}	-10 to $+60$	°C

* $V_{CC} = 5.0$ V

DC CHARACTERISTIC

(If there is no specification, V_{dd1} is 14.5 V, V_{dd2} is 1 V, V_{CC} is 5 V, grounding is 0 V, V_{SS} is -6 V, and T_a ranges from -10 to $+60$ °C.)

CHARACTERISTICS	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNIT
High Level Output Voltage (High level)	$V_{OH} (H)$	$V_I = GND, V_{CC} I_O = -1$ mA	$V_{DD1} - 0.1$		V_{DD1}	V
High Level Output Voltage (Middle level)	$V_{OH} (M)$	$V_I = GND, V_{CC} I_O = -1$ mA	$V_{DD2} - 0.1$		V_{DD2}	V
Low Level Output Voltage (Low level)	$V_{OL} (L)$	$V_I = GND, V_{CC} I_O = 1$ mA	$V_{SS} + 0.1$		V_{SS}	V
Input Current	I_I	$V_I = GND, V_{CC}$			1.0	μA
Output on Resistance (High level)	$R_{ON} (H)$	$I_O = -50$ mA		18	30	Ω
Output on Resistance (Middle level)	$R_{ON} (M)$	$I_O = -50$ mA		18	30	Ω
Output on Resistance (Low level)	$R_{ON} (L)$	$I_O = 50$ mA		18	30	Ω
Static Current Consumption	$I_{CC} + I_{DD1} + I_{DD2}$	$V_I = GND, V_{CC}$		10^{-4}	100	μA

AC CHARACTERISTIC

CHARACTERISTICS	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNIT
Transmission Delay Time	t_{PLH}, t_{PHL}	No load. See Figure 1.		100	200	ns
Transmission Delay Time	t_{PLH}, t_{PHL}	Middle level \longleftrightarrow High level		200	400	ns
Rising and Falling Time	t_{TLH}, t_{THL}	Load circuit. See Figure 2.		200	300	ns
Current Consumption	$I_{dyn} (I_{CC} + I_{DD1} + I_{DD2} + I_{SS})$	Input pulse timing is Figure 3.		6.0	10	mA
	I_{CC}			0.02	0.2	mA
	$I_{DD1} + I_{DD2}$			3.8	5.0	mA
	I_{SS}			-5.0	-3.8	mA

Fig. 1 Transmission Delay Time




Fig. 2 Output Load Circuit






Fig. 3 Input Pulse Timing Diagram




APPLICATION CIRCUIT EXAMPLE

CCD Camera Drive Block Diagram




SAMPLE APPLICATION CIRCUIT



Note 1. Turn on the power V_{DD1} before V_{CC} and V_{DD2}

2. PG_1 (terminal 9) and PG_2 (terminal 12) are able to input both common signal and different signal.

20PIN PLASTIC SOP (300 mil)



P20GM-50-300B,C-1

NOTE

Each lead centerline is located within 0.12 mm (0.005 inch) of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS	INCHES
A	13.00 MAX.	0.512 MAX.
B	0.78 MAX.	0.031 MAX.
C	1.27 (T.P.)	0.050 (T.P.)
D	0.40 ^{+0.10} / _{-0.05}	0.016 ^{+0.004} / _{-0.003}
E	0.1 ^{±0.1}	0.004 ^{±0.004}
F	1.8 MAX.	0.071 MAX.
G	1.55	0.061
H	7.7 ^{±0.3}	0.303 ^{±0.012}
I	5.6	0.220
J	1.1	0.043
K	0.20 ^{+0.10} / _{-0.05}	0.008 ^{+0.004} / _{-0.002}
L	0.6 ^{±0.2}	0.024 ^{+0.008} / _{-0.009}
M	0.12	0.005

[MEMO]

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.

NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or of others.