

ATGBICS SFP-GE-T Cisco Compatible Transceiver SFP 1000Base-T (Copper RJ45, Ext Temp, 100m)

Brand : ATGBICS

Product code: SFP-GE-T-C

Product name : SFP-GE-T Cisco Compatible Transceiver SFP 1000Base-T (Copper RJ45, Ext Temp, 100m)



SFP-GE-T Cisco Compatible Transceiver SFP 1000Base-T (Copper RJ45, Ext Temp, 100m)

ATGBICS SFP-GE-T Cisco Compatible Transceiver SFP 1000Base-T (Copper RJ45, Ext Temp, 100m):

ATGBICS SFP-GE-T 1000BASE-T SFP operates on standard Category 5 unshielded twisted-pair copper cabling of link lengths up to 100m. Note this 1000BASE-T SFP module does NOT support 10/100/1000 auto negotiation and auto MDI/MDIX. It is fixed at 1000Base-T. Our product meets the specification of Cisco SFP-GE-T= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



Performance		Power	
SFP transceiver type *	Copper	Input voltage	3.3 V
Maximum data transfer rate *	1000 Mbit/s	Maximum voltage	4 V
Interface type *	SFP	Power consumption (typical)	1.3 W
Single-mode fiber (SMF) supported	✗	Operational conditions	
Multi-mode fiber (MMF) supported	✗	Minimum operating temperature	-5 °C
SFP transceiver standard	TX	Maximum operating temperature	85 °C
Maximum transfer distance	100 m	Operating temperature (T-T)	-5 - 85 °C
Ethernet LAN	✓	Storage temperature (T-T)	-40 - 85 °C
Ethernet interface type	Gigabit Ethernet	Operating relative humidity (H-H)	5 - 85%
Copper ethernet cabling technology	1000BASE	Storage relative humidity (H-H)	5 - 85%
Auto MDI/MDI-X	✗	Weight & dimensions	
Digital Diagnostics Monitoring (DDM)	✗	Width	13.4 mm
Features		Depth	56.5 mm
Product colour	Silver	Height	8.5 mm
Housing material	Metal	Weight	20 g
Plug and Play	✓	Packaging data	
Hot-Plug support	✓	Number of products included	1 pc(s)
Hot-swap	✓	Package type	Box
Easy to install	✓	Technical details	
Country of origin	United Kingdom	Sustainability compliance	✓
Brand compatibility	Cisco	Sustainability certificates	RoHS
Certification	CE, FCC, RoHS	Doesn't contain	Lead



5056468701398

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date