

ASPIAIG-QLR5050

Request Samples



Check Inventory (>)



6.0 x 5.7 x 4.8 mm **RoHS/RoHS II Compliant** MSL Level = 1

Features

- PPAP ready and supported
- TS16949 certified production lines
- AEC-Q200 Grade 0 qualified (-55° C $\sim +155^{\circ}$ C)
- Shielded construction
- Soft saturation
- Low DCR, High Efficiency

Applications

- Body electronics and comfort system
- Infotainment and entertainment
- Electric vehicles
- Lighting
- Solar inverters and power
- Industrial and robotics
- Medium and high power switch mode power supplies.

Electrical Specifications

Part Number	Inductance	Tolerance	DC Resistance	Saturation Current	Temperature Rise Current
	0.1MHz/0.1V		Typ/Max		Max
Units	μН	%	m Ω	A	A
Symbol	L	M	DCR	Isat	Irms
ASPIAIG-QLR5050-5R6	5.6	M	22.0 / 24.2	7.2	7.2
ASPIAIG-QLR5050-6R8	6.8	M	26.0 / 28.6	6.6	6.4
ASPIAIG-QLR5050-8R2	8.2	M	29.5 / 32.5	6.1	6.1
ASPIAIG-QLR5050-100	10	M	39.0 / 43.0	5.4	5.0

Test Conditions

Isat: DC current at which the inductance drops 20% from its value.

Irms: DC current that causes the temperature rise (ΔT, approximate 40 °C) from 20 °C ambient

Operating Temperature: $-55^{\circ}\text{C} \sim +155^{\circ}\text{C}$ (including self-temperature rise)

Storage Condition: -55° C $\sim +155^{\circ}$ C and R.H. 60 max

Operating Voltage: 15V (across inductor)

ASPIAIG-QLR5050 Series is RoHS Compliant and Pb free

ASPIAIG-QLR5050 is AEC-Q200 Grade 0 qualified (-55°C ~ +155°C)

MSL level: 1





ASPIAIG-QLR5050

Request Samples (>)




Check Inventory (>)




6.0 x 5.7 x 4.8 mm **RoHS/RoHS II Compliant** MSL Level = 1

Marking



Marking Method: Ink

Part Identification







ASPIAIG-QLR5050

Request Samples (>)




Check Inventory (>)




6.0 x 5.7 x 4.8 mm RoHS/RoHS II Compliant MSL Level = 1

Mechanical Dimensions








Series	A	В	C	D	E	F
ASPIAIG-Q5030	6.0 ± 0.2	5.7 ± 0.2	4.8 ± 0.2	4.3 ± 0.3	1.1 ± 0.2	2.3 ± 0.25

Recommended Land Pattern



L Typ.	G Typ.	H Typ.
4.5	2.0	4.7

Dimensions: mm





ASPIAIG-QLR5050

Request Samples (>)




Check Inventory (>)



6.0 x 5.7 x 4.8 mm RoHS/RoHS II Compliant MSL Level = 1

Materials



	Components	Material
a	Core	Alloy powder
b	Wire	220 deg. C Flat Wire
с	Solder	100% Pb free solder
d	Ink	Halogen-free ketone





ASPIAIG-QLR5050

Request Samples (>)




Check Inventory (>)



6.0 x 5.7 x 4.8 mm RoHS/RoHS II Compliant MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$\begin{split} T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C \end{split}$	$60 \sim 180$ sec.
2	Reflow	T _L 217°C	$60 \sim 150 \text{ sec.}$
3	Peak heat	T _P 260°C±5°C	10 sec. MAX





ASPIAIG-QLR5050

Request Samples (>)




Check Inventory (>)




6.0 x 5.7 x 4.8 mm **RoHS/RoHS II Compliant** MSL Level = 1

Packaging

Tape & Reel: 1500 pcs/reel)



W	F	P	D	$\mathbf{A_0}$	\mathbf{B}_{0}	T	\mathbf{K}_{0}
16.0 ± 0.3	7.5 ± 0.1	8.0±0.1	1.5±0.1	6.4±0.1	6.1 ± 0.1	0.35 ± 0.05	5.3 ± 0.1



A	В	С	D
16.4+2/-0	100 ± 2	13.0+0.5/-0.2	330

Dimension: mm

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

