



NOTES:

1. MATERIALS & FINISH:
  - 1.1 HOUSING: PASSIVATED STAINLESS STEEL
  - 1.2 SUPPORT BEAD: ULTEM 1000
  - 1.3 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
2. SPECIFICATIONS:
  - 2.1 FREQUENCY RANGE: DC to 26.5 GHz
  - 2.2 IMPEDANCE: 50 OHMS NOMINAL
  - 2.3 VSWR (MAX):
    - 2.3.1 DC TO 20 GHz: 1.10:1
    - 2.3.2 20 TO 26.5 GHz: 1.15:1
  - 2.4 OPERATING TEMP RANGE: -65°C to +125°C



REV.	DESCRIPTION	DATE
-	RELEASED	8/29/84
A	ECR 3702	7/2/85
B	ECR 4398	3/21/86
C	ECR 6003	5/17/88
D	ECR 6545	7/31/89
E	REDRAW ON CAD	11/20/92
E1	ECO 23178	1/5/11
F	ECO 23394	3/17/11
G	ECO 57925	4/30/21

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.		CAGE CODE <b>34078</b>		<b>MIDWEST MICROWAVE</b>	
UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1'				TITLE <b>3.5mm FEMALE TO FEMALE ADAPTER</b>	
DRAWN/DATE A.BEATTY 11/20/92		ENG./DATE A.OSGA 11/20/92		DRAWING NUMBER ADT-2735-FF-3MM-02-01	
CHECKED/DATE M.HOLLMAN 11/20/92		APPROVED/DATE		REV. G	
SCALE: 3:1				SHEET 1 of 1	