
ANALOG BOTTOM PORT SISONIC™ MICROPHONE

The SPV1142LR5H-1 is a miniature, high-performance, low power, matched sensitivity bottom port silicon microphone. Using Knowles' proven high performance SiSonic[™] MEMS technology with a flat frequency response and low LFRO (Low Frequency Roll Off), the SPV1142LR5H-1 consists of an acoustic sensor, a low noise input buffer, and an output amplifier. These devices are suitable for applications such as Headsets, TWS and other portable electronic devices where excellent wideband audio performance is required.




ABSOLUTE MAXIMUM RATINGS

Table 1: Absolute Maximum Ratings

Parameter	Absolute Maximum Rating	Units
Vdd to Ground	-0.3, +5.0	V
OUT to Ground	-0.3, Vdd+0.3	V
Input Current	±5	mA
Storage Temperature	-40 to +100	°C
Operating Temperature	-30 to +100	°C

Stresses exceeding these "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only. Functional operation at these or any other conditions beyond those indicated under "Acoustic & Electrical Specifications" is not implied. Exposure beyond those indicated under "Acoustic & Electrical Specifications" for extended periods may affect device reliability.

Knowles



PRODUCT FEATURES

- Matched Sensitivity
- LGA Package
- Flat Frequency Response
- Low Current
- RF Shielded
- Bottom Port
- Ultra-Stable Performance
- Omnidirectional
- Standard SMD Reflow

TYPICAL APPLICATIONS

- Headsets
- TWS





ACOUSTIC & ELECTRICAL SPECIFICATIONS¹

Table 2: General Microphone Specifications


Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8V, no load, unless otherwise indicated


Parameter	Symbol	Conditions	Min	Тур	Max	Units
Supply Voltage	Vdd		1.5	1.8	3.6	V
Queralu Querrant	Islal	Vdd = 3.6 V	-	145	185	
Supply Current	ldd	Vdd = 1.8V	-	132	165	μA
Sensitivity	S	94 dB SPL @ 1kHz	-39	-38	-37	dBV/Pa
Signal to Noise Ratio	SNR	94 dB SPL @ 1kHz, A-weighted	-	63	-	dBV/Pa
Near-Ultrasonic SNR		94 dB SPL, @ 19 kHz , BW = 18.5 - 20.0 kHz	-	75	-	dB
		94 dB SPL @ 1 kHz	-	0.15	-	%
Total Harmonic Distortion	THD	115 dB SPL @ 1 kHz	-	2	-	%
		1% THD @ 1 kHz, S = typ	-	108	-	dB SPL
Acoustic Overload Point	AOP	10% THD @ 1 kHz, S = typ	-	123	-	dB SPL
Low Frequency Rolloff	LFRO	-3dB relative to 1 kHz	-	25	-	Hz
High Frequency Flatness		+3dB relative to 1 kHz	-	16	-	kHz
Resonant Frequency Peak	Fres		-	27	-	kHz
Power Supply Rejection Ratio	PSRR	200 mVpp sinewave @ 1 kHz, Single-Ended Mode	-	75	-	dB
Power Supply Rejection	PSR+N	200 mVpp 7/8 duty cycle rectangular waveform @ 217 Hz, A-weighted, Single-Ended	-	-97	-	dBV(A)
DC Output		Vdd = 1.8V	-	1.1	-	V
Output Impedance	Zout	@ 1 kHz	-	300	400	Ω
Output	Cload		-	-	260	pF
Output Load	Rload	AC-coupled	7	-	-	kΩ
Sensitivity Drop		Vdd(min) ≤ Vdd ≤ Vdd(max)	-	-	±0.25	dB
Directivity			Omnidirectional			
Polarity		Increasing sound pressure	Increasing	Output Volta	ge	
Startup Time		S within 1 dB of final value, outputs AC coupled	-	-	50	ms

¹ Sensitivity and Supply Current are 100% tested.










If necessary to improve RF performance, optional series components (resistors, ferrites, etc.) should be placed closest to the microphone pads. Bypass capacitors should be placed near each Vdd pin for best performance. Capacitors near the microphone should not contain Class 2 dielectrics due to their piezoelectric effect. Follow the codec manufacturer's recommendations for circuitry and layout.


PERFORMANCE CURVES


Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8V, no load, unless otherwise indicated




-1

LSL








94dB SPL

1,000

Frequency (Hz)





knowles.com | DATASHEET SPV1142LR5H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.

0.1

100

10,000



Figure 7: Typical Free Field Ultrasonic Response




Figure 8: Typical Idd vs Vdd






Figure 9: Noise Floor Power Spectral Density









knowles.com | DATASHEET SPV1142LR5H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.






MECHANICAL SPECIFICATIONS









Item	Dimension	Tolerance
Length (L)	2.75	±0.10
Width (W)	1.85	±0.10
Height (H)	0.90	±0.10
Acoustic Port (AP)	Ø0.25	±0.05
PCB Thickness (T)	0.285	-0.035, +0.05

Pin #	Pin Name	Туре	Description
1	Vdd	Power	Power Supply
2	OUT	Signal	Output
3	GROUND	Power	Ground
4	No Connect	N/A	Test Pin - do not place over ground plane


Example Land Pattern



Example Solder Stencil Pattern



NOTES



Pick Area only extends to 0.25 mm of any edge or hole unless otherwise specified. Dimensions are in millimeters unless otherwise specified. Tolerance is ±0.15mm unless otherwise specified.


In the acoustic path, the recommended PCB Hole Diameter is $0.6 \le D \le 1.0$ mm, the recommended Gasket Cavity Diameter is $D \ge 1.0$ mm and the recommended Case Hole Diameter is $1.0 \le D \le 1.5$ mm. Further optimizations based on application should be performed.

knowles.com | DATASHEET SPV1142LR5H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.






PACKAGING & MARKING DETAIL



Model Number	Suffix	Reel Diameter	Quantity Per Reel
SPV1142LR5H-1	-8	13"	5,900

Component	Surface Resistance (ohms)
Reel	10 ⁵ - 10 ⁹
Carrier Tape	10 ⁵ - 10 ⁹
Cover Tape	10 ⁴ - 10 ¹⁰



NOTES

Dimensions are in millimeters unless otherwise specified.

Vacuum pickup only in the pick area indicated in Mechanical Specifications. Tape & reel per EIA-481.

Labels applied directly to reel and external package.

Shelf life: Twelve (12) months when devices are stored in the factory-supplied, unopened ESD moisture sensitive bag under the maximum environmental conditions of 30°C, 70% R.H.

knowles.com | DATASHEET SPV1142LR5H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.

2D barcode "ABCDEFGHJKLMNPORSTUVWXYZ0123456789": Unique Job Identification Number for product traceability

Letter: "o", orientation mark (pin 1)


"C": Knowles Factory KES2 "P": Knowles KEI

Date Code YWW: "Y": Last digit of year "WW": Work week AA = Internal Knowles Code F = Factory Location: "M": Knowles Factory KEM3





RECOMMENDED REFLOW PROFILE



Profile Feature	Pb-Free
Average Ramp-up rate (T_{SMAX} to T_P)	3°C/second max.
Preheat Temperature Min (T_{SMIN}) Temperature Max (T_{SMAX}) Time (T_{SMIN} to T_{SMAX}) (t_S) 	150°C 200°C 60-180 seconds
Time maintained above: • Temperature (T _L) • Time (t _L)	217°C 60-150 seconds
Peak Temperature (T _P)	260°C
Time within 5°C of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down rate (T _P to T_{SMAX})	6°C/second max
Time 25°C to Peak Temperature	8 minutes max

NOTES

Based on IPC/JEDEC J-STD-020 Revision C.

All temperatures refer to topside of the package, measured on the package body surface.

The actual reflow profile used should be optimized based on the reflow requirements of all components, board design, solder paste formulation and reflow equipment used. Details of recommended handling and manufacturing processes can be found in AN25 SMT Manufacturing Guidelines for SiSonic™ Microphones.

ADDITIONAL NOTES

- (A) MSL (moisture sensitivity level) Class 1.
- (B) Maximum of 3 reflow cycles is recommended.
- C) In order to minimize device damage:
 - Do not board wash or clean after the reflow process.
 - Do not brush board with or without solvents after the reflow process.
 - Do not directly expose to ultrasonic processing, welding, or cleaning.
 - Do not insert any object in port hole of device at any time.
 - Do not apply over 30 psi of air pressure into the port hole.
 - Do not pull a vacuum over port hole of the microphone.
 - Do not apply a vacuum when repacking into sealed bags at a rate faster than 0.5 atm/sec.
 - Do not directly expose to vapor phase soldering.

knowles.com | DATASHEET SPV1142LR5H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.





MATERIALS STATEMENT

Meets the requirements of the European RoHS directive 2011/65/EC as amended.

Meets the requirements of the industry standard IEC 61249-2-21:2003 for halogenated substances and Knowles Green Materials Standards Policy section on Halogen-Free.

Product is Beryllium Free according to limits specified on the Knowles Hazardous Material List (HSL for Products).

Ozone depleting substances are not used in the product or the processes used to make the product, including compounds listed in Annex A, B, and C of the "Montreal Protocol on Substances That Deplete the Ozone Layer.

RELIABILITY SPECIFICATIONS

Test	Description
Thermal Shock	100 cycles of air-air thermal shock from -40°C to +125°C with 15 minute soaks (IEC 68-2-14)
High Temperature Storage	+105°C environment for 1,000 hours (JESD22-A103)
Low Temperature Storage	-40°C environment for 1,000 hours (JESD22-A119)
High Temperature Bias	+105°C environment while under bias for 1,000 hours (JESD22-A108)
Low Temperature Bias	-40°C environment while under bias for 1,000 hours (JESD22-A108)
Temperature/Humidity Bias	+85°C/85% R.H. environment while under bias for 1,000 hours (JESD22-A101A-B)
Vibration	16 minutes in each X, Y, Z axis from 20 to 2,000 Hz with peak acceleration of 20g (MIL STD-883e, Method 2007.2, Condition A)
ESD-HBM	3 discharges at ±2kV direct contact to I/O pins (ANSI/ESDA/JEDEC JS-001-2014)
ESD-HMM	10 discharges at ±8kV direct contact to lid when unit is grounded (ANSI/ESD SP5.6-2009)
ESD-CDM	3 discharges at ±500V (ANSI/ESDA/JEDEC JS-002-2014)
Reflow	5 reflow cycles with peak temperature of +260°C (JEDEC 22-A113F)
Mechanical Shock	3 pulses of 12,000g in each of the X, Y, and Z directions (IEC 68-2-27 Test Ea)

NOTES:

Microphones meet all acoustic and electrical specifications before and after reliability testing, except sensitivity which can deviate up to 3dB.

After 3 reflow cycles, the sensitivity of the microphones shall not deviate more than 1 dB from its initial value





SPECIFICATION REVISIONS

Revision	Specification Changes	Date
А	Initial Release (ECR 21-4221)	3/4/21

Information contained herein is subject to change without notice. It may be used by a party at their own discretion and risk. We do not guarantee any results or assume any liability in connection with its use. This publication is not to be taken as a license to operate under any existing patents.

Knowles Corporation 1151 Maplewood Drive Itasca, Illinois 60143 Phone: 1 (630) 250-5100 Fax: 1 (630) 250-0575 sales@knowles.com Model/Reference Number: Datasheet SPV1142LR5H-1 Rev A © Copyright 2021 Knowles

