









### **Features**

- Best combination of price and performance
- For general commercial use
- Up to 18 GHz operation
- Gold and nickelplated brass construction
- SMA to SMA, SMA to N, SMA to MCX, male/female versions
- Bulkhead SMA female to SMA female also available



# **Applications**

- Cellular base stations
- Public safety systems
- Wi-Fi networks hardware
- Active antenna systems
- 5G network hardware
- GPS systems

## **Electrical**

	SMA to SMA Models	SMA to N Models	SMA to MCX Models
Frequency of Operation	DC-18 GHz	DC-10 GHz	DC-6 GHz
Impedance	50Ω (Nominal)	50Ω (Nominal)	50Ω (Nominal)
VSWR	1.2:1 (max.)	1.2:1 (max.)	1.2:1 (max.)

### **Materials and Finish**

Body	Gold plated brass	Nickel plated brass	Gold plated brass
Male Center Contact	Gold plated brass	Gold plated brass	Gold plated brass
Female Center Contact	Gold plated beryllium copper	Gold plated beryllium copper	Gold plated beryllium copper
Insulator	PTFE	PTFE	PTFE

## **Environmental**

O 11 T	1000 1 0500	4000 1 0500	4000 1 0500
Operating Temperature	-40°C to +85°C	-40°C to +85°C	-40°C to +85°C






### **SMA Male to MCX Female**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1060-SM-MCF-09	Gold Plated	50 Ohms	DC - 6 GHz	1.20 Max






## **SMA Male to MCX Male**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1060-SM-MCM-09	Gold Plated	50 Ohms	DC - 6 GHz	1.20 Max






## **SMA** Female to MCX Female

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1060-SF-MCF-09	Gold Plated	50 Ohms	DC - 6 GHz	1.20 Max










### **SMA Female to MCX Male**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1060-SF-MCM-09	Gold Plated	50 Ohms	DC - 6 GHz	1.20 Max






# **SMA Male to N Female Adapter**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1100-NF-SMM-10	Gold Plated	50 Ohms	DC - 10 GHz	1.20 Max






# **SMA Male to N Male Adapter**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1100-NM-SMM-10	Gold Plated	50 Ohms	DC - 10 GHz	1.20 Max










## **SMA Female to N Female Adapter**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1100-NF-SMF-10	Gold Plated	50 Ohms	DC - 10 GHz	1.20 Max






# **SMA Female to N Male Adapter**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1100-NM-SMF-10	Gold Plated	50 Ohms	DC - 10 GHz	1.20 Max






## **SMA Male to SMA Female**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1180-MF-SMA-0	9 Gold Plated	50 Ohms	DC - 18 GHz	1.20 Max










#### **SMA Male to SMA Male**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1180-MM-SMA-09	Gold Plated	50 Ohms	DC - 18 GHz	1.20 Max






### **SMA Female to SMA Female**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1180-FF-SMA-09	Gold Plated	50 Ohms	DC - 18 GHz	1.20 Max






## **SMA Female to SMA Female Bulkhead**

Part Number	Material	Impedance	Maximum Frequency	VSWR
CGM-1180-FB-SMA-09	Gold Plated	50 Ohms	DC - 18 GHz	1.20 Max







Asia Pacific +86 21 5442 7668 ccs.asia.sales@as.cinch.com Europe, Middle East & Africa +44 (0) 1245 342060 cinchconnectivity@eu.cinch.com North America +1 507 833 8822 ccsorders@us.cinch.com

belfuse.com/cinch