		REVISIONS					
The second secon		REV.	DESCRIPTION	DATE	APPROVED		
CALL		A	INITIAL RELEASE	04/03/18	C.E.		
	.344 HEX		.120				

NOTES:

MATERIALS:

- INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
 ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
 ALL OTHER MÉTAL PARTS = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200µin THICK OVER 50 TO 100µin THICK COPPER PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: DATE C.E. 04/03/1 CHKD: DATE		C	Property of This document cannot communicated to a thin written permission of R	be reproduc rd party wi		C
DECIMAL	ANGLE	D.N. 04/03/1			SCREW-ON		le plu	G
		APVD: DATE			CLAMP TY			
		J.M. 04/03/1	⁸ FOI	r rg-	-316 & SIM	ILAR	CABLES	\$
REFERENCE: ORIGINATED: C.E.		MATERIALS & FINISHES: SEE NOTES	SIZE A	FSCM NO. 19505	DWG NO. 1702-7	7551	-003	rev A
DATE: 04/03/18		SEE NOTES	SCALE	4:1	THIRD ANGLE PROJECTION		SHEET 1 OI	F 1