

UNi-directional TVS Diodes Array

SOT-23 Plastic-Encapsulate ESD Protection Diodes

DESCRIPTION

The SMxx Series is designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.

This series has been specifically designed to protect sensitive components which are connected to power $\sqrt{}$ data and transmission lines from overvoltage caused by ESD(electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).


Features

- ♦ 350 Watts Peak Pulse Power per (8/20µs)
- ◆ IEC61000-4-2 (ESD) ±15kV (air), ±8kV (contact)
- IEC61000-4-4 (EFT) 40A (5/50ns)
- Protects one bidirectional line or two unidirectional lines
- Low clamping voltage
- Low leakage current
- Working voltages : 3V, 5V, 8V, 12V, 15V, 18V, 20V, 24V, 36V
- Meets MSL 1 Requirements

Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Networking and Telecom
- Serial and Parallel Ports
- Peripherals

Pin Configuration ROHS



Mechanical Characteristics

- ♦ Package: SOT-23
- ◆ Flammability Rating: UL 94V-0
- Terminal: Matte tin plated.
- High temperature soldering guaranted: 260°C/10s
- Packaging: Tape and Reel

Absolute Maximum Ratings (T_A=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	Vesd	± 15 ± 8	KV
Peak Pulse Power(tp=8/20us waveform)	P _{PP}	350	W
Operating Temperature	T _{OPT}	−55 to +150	°C
Storage Temperature	Тѕтс	−55 to +150	°C
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260(10 sec.)	°C

The above data are for reference only.



SMxx Series

UNi-directional TVS Diodes Array

Electrical Characteristics (TA=25°C unless otherwise specified)

PART NUMBER	DEVICE MARKING	V _{RWM} (V)	V _B (V)	I _⊤ (mA)	Vc@1A (V)	V, (V	′)	Ι _R (μΑ)	C _T (pF)
		(max.)	(min.)		(max.)	(max.)	(@A)	(max.)	(max.)
SM03	M03	3.3	4	1	7.0	14	20	40	450
SM05	M05	5	6	1	9.8	18	17	10	300
SM08	M08	8	8.5	1	13.4	24	15	2	240
SM12	M12	12	13.3	1	19	32	11	1	130
SM15	M15	15	16.7	1	24	38	10	1	120
SM18	M18	18	20.0	1	29	45	9	1	100
SM20	M20	20	22.3	1	35	50	8	1	90
SM24	M24	24	26.7	1	43	52	7	1	80
SM36	M36	36	40	1	60	75	5	1	60


The above data are for reference only.




SMxx Series


UNi-directional TVS Diodes Array

ELECTRICAL CHARACTERISTICS CURVE





Pulse Waveform




The curve above is for reference only .



SMxx Series UNi-directional TVS Diodes Array


Dimensions In Millimeters

SOT-23 Package Outline Dimensions



Symbol	Min	Тур	Max
А	0.89	1.00	1.40
A1	0.01	0.06	0.10
b	0.37	0.44	0.50
С	0.09	0.13	0.20
D	2.80	2.90	3.10
E	1.20	1.30	1.60
E1	2.10	2.40	2.80
е	1.78	1.90	2.04
L	0.10		0.30
L1	0.35	0.54	0.69
θ	0°		10°

Suggested Pad Layout



Note:

1. Controlling dimension:in/millimeters.

2. General tolerance: ±0.05mm.


Symbo


3. The pad layout is for reference purposes only.



SMxxC Series **Bi-directional TVS Diodes Array**

SOT-23 Tape and Reel






Packaging Description:


SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film,adhesive laye,sealant, and anti-static sprayed agent. These reeled parts In standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).


Dimensions are in millimeter										
Pkg type A B C d E F P0 P P1 W									W	
SOT-23	3.15	2.77	1.22	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

SOT-23 Tape Leader and Trailer









Dimensions are in millimeter									
Reel Option	D	D1	D2	G	Н	I	W1	W2	
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30	

W1

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 Inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	