



MBR3020CT THRU MBR30100CT

Reverse Voltage - 20 to 100 Volts Forward Current - 30.0 Ampere


SCHOTTKY BARRIER RECTIFIER

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Construction utilizes void-free molded plastic technique
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 250°C, 0.25" (6.35mm) from case for 10 seconds

Mechanical Data

Case : JEDEC TO-220AB Molded plastic body
Terminals : Solder plated, solderable per MIL-STD-750, Method 2026
Polarity : Polarity symbol marking on body
Mounting Position : Any
Weight : 0.080 ounce, 2.24 grams



Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD MBR 3020CT	MDD MBR 3030CT	MDD MBR 3040CT	MDD MBR 3045CT	MDD MBR 3050CT	MDD MBR 3060CT	MDD MBR 3070CT	MDD MBR 3080CT	MDD MBR 3090CT	MDD MBR 30100CT	UNITS
Maximum repetitive peak reverse voltage	V_{RMM}	20	30	40	45	50	60	70	80	90	100	V
Maximum RMS voltage	V_{RMS}	14	21	28	32	35	42	49	56	63	70	V
Maximum DC blocking voltage	V_{DC}	20	30	40	45	50	60	70	80	90	100	V
Maximum average forward rectified current (see fig.1)	$I_{(AV)}$	30.0										A
Peak forward surge current 8.3ms single half sine-wave	I_{FSM}	250										A
Maximum instantaneous forward voltage at 15.0A	V_F	0.55			0.75			0.85			V	
Maximum DC reverse current at rated DC blocking voltage	I_R	1.0										mA
$T_A=25^\circ C$ $T_A=100^\circ C$		15.0					50.0					
Typical junction capacitance (NOTE 1)	C_J	750					500					pF
Typical thermal resistance (NOTE 2)	$R_{\theta JC}$	2.0										°C/W
Operating junction temperature range	T_J	-50 to +125					-50 to +150					°C
storage temperature range	T_{STG}	-50 to +150										°C

Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2. Thermal resistance from junction to case.




MBR3020CT THRU MBR30100CT

Reverse Voltage - 20 to 100 Volts Forward Current - 30.0 Ampere

Ratings And Characteristic Curves

AVERAGE FORWARD RECTIFIED CURRENT, AMPERES

FIG. 1- FORWARD CURRENT DERATING CURVE



PEAK FORWARD SURGE CURRENT, AMPERES

FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT





FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS



INSTANTANEOUS REVERSE CURRENT, MILLIAMPERES

FIG. 4-TYPICAL REVERSE CHARACTERISTICS






FIG. 5-TYPICAL JUNCTION CAPACITANCE



TRANSIENT THERMAL IMPEDANCE, °C/W

FIG. 6-TYPICAL TRANSIENT THERMAL IMPEDANCE



The curve above is for reference only.