






STRAIGHT PLUG CRIMP TYPE CABLE 3.8/93

PAGE 1/2 ISSUE 26-03-15C SERIES BNC 75-COM PART NUMBER R142078161







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body	BRASS	NICKEL	
,			
Center contact	BRASS	GOLD OVER NICKEL	
Outer contact	BRASS	NICKEL	
Insulator	POLYPROPYLENE		
Gasket	SILICONE RUBBER		
Others parts	BRASS	NICKEL	
-	-	-	
-	-	-	



Technical Data Sheet

STRAIGHT PLUG CRIMP TYPE CABLE 3.8/93

PAGE **2/2** ISSUE 26-03-15C SERIES BNC 75-COM PART NUMBER **R142078161**

PACKAGING

Standard	Unit	Other
100	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

Impedance 75 Ω Frequency 0-1.5 GHz VSWR NA 0.0000 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss NΑ RF leakage NA - F(GHz)) dB Maxi Veff Maxi Voltage rating 500 Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End 10 N mini Axial force - Opposite end 10 N mini NA N.cm mini Torque

Recommended torque

Mating NA N.cm Panel nut NA N.cm Clamp nut NA N.cm 0.0000 A/F clamp nut mm

Mating life 100 Cycles mini g

Weight 0.0000

ENVIRONMENTAL

-35/+70 °C Operating temperature Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	4	10.5	17.5	0	13.5	0

Assembly instruction: Clamp 02

Recommended cable(s)

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off 110 N mini - torque NA N.cm

TOOLING

Part Number	Description	Hexagon	
R282235011	CRIMPING DIES M22520/5-11	1.73 - 6.48	
R282293000	CRIMPING TOOL M22520/5-01	-	
R282223000	CRIMPING TOOL	1.73 - 6.48	

OTHER CHARACTERISTICS