





注：本板为禁止运输、复制、编辑文件，以及用其内容进行交流



REV	ECN NO.	CONTENT	CHK	DATE

NOTES1:

- UL Standard
- 1.Rating voltage/current: 300V/8A
- 2. withstanding voltage: AC2000V/1Min
- 3. Torque value: M2.0, 1.77Lbin
- 4. Wire range: 28~16AWG

IEC Standard

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	7A	7A	7A

- 2. Torque value: M2, 0.2Nm
- 3. wire range: 0.5~1.5mm²

NOTES2:

- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Cage: Brass (Ni Plated)
- 4.Clamp: Copper alloy (Ni Plated)
- 5.Screw: Steel (M2.0,Zn Plated)

NOTES3:

- 1.Pitch: 3.81mm Poles: 02-24P
- 2.Stripping length: 6-7mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MX15EDGK - 381 - XXX - XXXX - XX - X - X

产品型号

间距

颜色

极数

01常规颜色
02-99:定制颜色

A-Z其他定制

0-Y一字螺丝
1-S十字螺丝
2-P.S平头十字螺丝

- 灰色:GY 橙色:OE
- 蓝色:BU 红色:RD
- 黑色:BK 透明色:TT
- 绿色:GN 黄色:YW
- 透明色:TT 白色:WE

Cu:铜方块
Fe:铁方块

Pitch Range In Nominal Dimension Range

mm	Over	In mm	Over	Nominal Dimension Range	Over	mm	Over
6	TO	6	TO	30	TO	60	TO
10	TO	10	TO	60	TO	100	TO
24	TO	24	TO	100	TO	150	TO
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30

—	∩	∇
---	---	---

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	UNITS	MM	1/1
APP	DATE	SCALE	A4		

NAME: MX15EDGK-3.81-XXX