

Radiall 狐

RIGHT ANGLE PLUG CRIMP TYPE CABLE 4.13/50

PAGE 1/3 ISSUE **03-11-15D** SERIES TNC PART NUMBER **R143191700** 49.2 Ø4.4 41.2 □ 11 \ Ø2.7 25.9 Ø 1.15 20.2 8 / 2 flats  $\emptyset$ 11.5 10 / 2 flats 10 / 2 flats Hex. 14 / flats Protective Cap 3 safety holes of Ø 0.95 Scale: 1/1 All dimensions are in mm.

COMPONENTS MATERIALS		PLATING (μm)	
Body	STAINLESS STEEL.	PASSIVATED.	
Center contact	BERYLLIUM COPPER,BRASS	GOLD 0.5 OVER NICKEL 2	
	BERTELION COLLER, BRASS		
Outer contact	<del>-</del>	•	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Others parts	STAINLESS STEEL	PASSIVATED.	
-	-	-	
-	-	-	



# **Technical Data Sheet**

RIGHT ANGLE PLUG CRIMP TYPE CABLE 4.13/50

PAGE 2/3 ISSUE 03-11-15D SERIES TNC PAI	RT NUMBER <b>R143191700</b>
-----------------------------------------	-----------------------------

#### **PACKAGING**

1	Contact us	Contact us
Standard	Unit	Other

#### **ELECTRICAL CHARACTERISTICS**

Impedance 50 Ω Frequency 0-6 GHz **VSWR** 1.35 0,0000 x F(GHz) Maxi Insertion loss 0.1 √F(GHz) dB Maxi RF leakage 57\* - F(GHz)) dB Maxi - ( Voltage rating Veff Maxi 500 Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000  $M\Omega$  mini

#### **MECHANICAL CHARACTERISTICS**

Center contact retention

Axial force - Mating End 27 N mini Axial force - Opposite end 27 N mini N.cm mini NA Torque

Recommended torque

265 Mating N.cm Panel nut NA N.cm Clamp nut N.cm 170 A/F clamp nut 8,0000 mm

500 Mating life Cycles mini g

Weight 30,4000

#### **ENVIRONMENTAL**

-65/+165 Operating temperature °C Hermetic seal NA Atm.cm3/s Panel leakage NA

#### **SPECIFICATION**

### CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	9	9	23	0	0	0

Assembly instruction:

Recommended cable(s)

FILECA F1703-93 **50 PFCFB FILOTEX** 

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the

Cable retention

- pull off 180 N mini NA - torque N.cm

#### **TOOLING**

Part Number	Description	Hexagon	
R282246000	CRIMPING DIES M22520/5-05	5.41	
282291	CRIMPING TOOL M22520/1-01	2x4 (pos 7)	
R282293000	CRIMPING TOOL M22520/5-01	-	
282997	POSITIONER FOR TOOL 282.291(M22520/1-13)	rouge	

#### **OTHER CHARACTERISTICS**

\* Up to 3 GHz






RIGHT ANGLE PLUG CRIMP TYPE CABLE 4.13/50

PAGE **3/3** 

ISSUE **03-11-15D** 

SERIES TNC

## PART NUMBER **R143191700**




1

Slide onto the cable the heatshrink sleeve and the ferrule

Strip the cable.

Cut the foil under the braid for the FILECA cable.

Optionally, to facilitate the stripping of the inner cable, the length "a" could be stripped after crimping of the ferrule.




2

Slide the clamp nut onto the crimp sleeve.

Slide sub-assembly under the braid.

Slide ferrule over the braid against clamp nut.(In direction F) Crimp the ferrule with crimping tool + dies



3

The dielectric must be in the same plane as the face of the crimp sleeve. Cut the dielectric flush to crimp sleeve if it exceeds.

Clean the dielectric side.

Mount insulator against crimp sleeve.



4

Slide the center contact onto the cable inner conductor against insulator.

Crimp the center contact with the crimping tool and the positioner.



5

Screw sub-assembly into the connector body. (recommended coupling see the connector TDS) Slide sleeve heatshrink over ferrule and put in the place as below

