



NOTES:

1. MATERIALS AND FINISHES:
 - COUPLING NUT - BRASS, NICKEL PLATING
 - BODY - BRASS, NICKEL PLATING
 - OTHER METAL PARTS - BRASS, NICKEL PLATING
 - CONTACT - BRASS, GOLD PLATING
 - INSULATOR & RING - DELRIN, NATURAL
 - GASKE - SILICONE RUBBER, RED
2. ELECTRICAL:
 - A. IMPEDANCE: 75 OHM
 - B. FREQUENCY RANGE: 0-2 GHz
 - C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -40°C TO +85°C

THIRD ANGLE PROJ.



REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	20-Jul-08	-----	SH
B	THE BODY WAS CHANGED/RD-DM11111001I	28-Nov-11	-----	SH
C	SYNC, ADDED THE P/N	19-Sep-19	12981	SH



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ±0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°	MATERIAL	DRAWN	DATE	TITLE TNC MALE TO TNC MALE ADAPTOR (75 OHMS)	Amphenol RF www.amphenolrf.com
	SEE NOTES	M. ZHANG	19-Sep-19		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	S. LI	DATE	SCALE: 7.0:1.0 SHEET 2 OF 2	DRAWING NO. T2071A2-ND3G-75
	EAR#	S. HSIEH	19-Sep-19		REV C
	REF:	CONFIGURATION LEVEL: In Work	CAD FILE		
FINISH					