







STRAIGHT BULKHEAD JACK PANEL SEAL SOLDER TYPE-CABLE .085

PAGE 1/2 ISSUE 20-01-17L SERIES TNC PART NUMBER 6001-7041-010









All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Dark	PRACE	NICKE
Body	BRASS	NICKEL
Center contact	BERYLLIUM COPPER	GOLD
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Others parts	PHOSPHOR BRONZE	NICKEL
-	-	-
-	-	-
		I control of the second of the



Technical Data Sheet

STRAIGHT BULKHEAD JACK PANEL SEAL SOLDER TYPE-CABLE .085

PAGE 2/2	ISSUE 20-01-17L	SERIES TNC	PART NUMBER 6001-7041-010

PACKAGING

100	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

Impedance 50 Ω Frequency 0-6 GHz **VSWR** 1.15 0.0000 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss 0.04 RF leakage N/A - F(GHz)) dB Maxi - (Voltage rating 500 Veff Maxi Dielectric withstanding voltage 100 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End 18 N mini Axial force - Opposite end 18 N mini N.cm mini 2.8 Torque

Recommended torque

N/A Mating N.cm Panel nut N/A N.cm Clamp nut N.cm 70 A/F clamp nut 0.0000 mm

Mating life 500 Cycles mini g

Weight 19.6300

ENVIRONMENTAL

-65/+105 Operating temperature °C Hermetic seal N/A Atm.cm3/s Panel leakage IP67

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	0	0	0	0	0	0

Assembly instruction: AIS-263-B

Recommended cable(s)

KS₁

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the

Cable retention

130 - pull off N mini N/A - torque N.cm

TOOLING

Part Number	Description	Hexagon

OTHER CHARACTERISTICS