


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	ECO #4407	01/24/02	A.D.M.




**NOTES:**

**MATERIALS:**

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. CONTACTS = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

**FINISHES:**

1. CONTACTS = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.
2. ALL OTHER METAL PARTS = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON	DWN. A D.M.	DATE 01/23/02	 <b>APPLIED ENGINEERING PRODUCTS</b> 104 John W. Murphy Dr. New Haven, CT 06513
	CHKD: G.A.T.	DATE 01/24/02	
DECIMAL	ANGLE	APVD: D.J.C.	DATE 01/24/02
REFERENCE:		<b>SSMB RIGHT ANGLE MALE JACK SURFACE MOUNT RECEPTACLE</b>	
ORIGINATOR: D.N. DATE: 01/23/90		MATERIALS & FINISHES: SEE NOTES	SIZE: A FSCM NO.: 19505 DWG NO.: 7210-1511-015 REV: A
		SCALE: 10:1	SHEET 1 OF 1

7210-1511-015