






STRAIGHT SQUARE FLANGE JACK SOLDER TYPE CABLE .141


PAGE 1/3 ISSUE 10-03-16B SERIES 4.3-10 PART NUMBER R183252007









DETAIL A SCALE 3 : 1







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	BBR
Center contact	BRONZE	SILVER
Outer contact	BRONZE	SILVER
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Others parts		
-	-	-
-	-	-



Technical Data Sheet

STRAIGHT SQUARE FLANGE JACK SOLDER TYPE CABLE .141

PAGE 2/3	ISSUE 10-03-16B	SERIES 4.3-10	PART NUMBER R183252007
-----------------	------------------------	----------------------	-------------------------------

PACKAGING

Standard	Unit	Other
50	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

50 Impedance Ω Frequency 0-6 GHz **VSWR** 1.02 0.0100 x F(GHz) Maxi Insertion loss 0.05 √F(GHz) dB Maxi RF leakage NA - F(GHz)) dB Maxi - (Veff Maxi Voltage rating 500 Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

 Axial force – Mating End
 30
 N mini

 Axial force – Opposite end
 30
 N mini

 Torque
 NA
 N.cm mini

Recommended torque

 Mating
 NA
 N.cm

 Panel nut
 NA
 N.cm

 Clamp nut
 NA
 N.cm

 A/F clamp nut
 0.0000
 mm

Mating life 100 Cycles mini

Weight **35.4430** g

ENVIRONMENTAL

Operating temperature -55~+90 °C
Hermetic seal NA Atm.cm3/s
Panel leakage IP67

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	2.17	0	0	0	0	0

Assembly instruction: NA

Recommended cable(s)

BELDEN 1673A Flexiform 402 MB

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

TOOLING

Part Number	Description	Hexagon
R282053000	STRIPPING TOOL	
R282066000	POINTER GAUGE	
R282740000	SOLDERING MOUNTING	

OTHER CHARACTERISTICS

PIM3<=-123 dBm, 2 carriers of +43dBm






STRAIGHT SQUARE FLANGE JACK SOLDER TYPE CABLE .141


PAGE 3/3 ISSUE 10-03-16B SERIES 4.3-10 PART NUMBER R183252007

COMPONENTS

BODY




STRIPPING DIMENSION



1

- -Strip the cable with the cable stripping tool.
- -Trim the cable inner conductor with the trimmer.
- -Clean the cable



2

- -Introduce the cable into the body until contact with the body shoulder.
- -Place the sub-assembly on assembly jig
- -Solder body on the cable.
- -Let assembly cool down before removing it from the jig.

