



## NOTES:

## MATERIALS:

- 1. RETAINING RING = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
  2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
  3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.
  4. GASKET = SILICONE RUBBER PER ZZ-R-765, CLASS 2B, GRADE 65-75.

## FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

  2. SOLDER FITTING = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

  3. ALL OTHER METAL PARTS = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200µin THICK OVER 50 TO 100µin THICK COPPER PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	AFR	Property of Radiall					
		D.N. 05/07/18		This document cannot be reproduced or						
		CHKD:	DATE	communicated to a third party without prior a RADIALL company written permission of RADIALL.						
DECIMAL	ANGLE	C.E.		TNC STRAIGHT PLUG						
		APVD:	DATE	SOLDER TYPE						
		J.M.	05/07/18	FOR	.085	S/R &	SIMILAR	CABLE	S.	
REFERENCE:		MATERIALS & F	INISHES:	SIZE	FSCM NO.	DWG NO.	7011	0.4.0	REV	
ORIGINATED: D.N. DATE: 05/07/18		SEE NOTES		А	19505	6000	-7041	-010	Α	
				SCALE 4:1		THIRD ANGLI PROJECTIOI	₩ ⊕ <del>[-]</del>	SHEET 1 O	)F 1	