



- BODY & NUT = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B". CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.

FINISHES:

- CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

	UNLESS OTHERWISE SPECIFIED		DWN: DATE	-	AEB 3	-	Property of Radiall	A	
	DIMENSIONS ARE IN		C.E. 03/15,	/18	VE.		his document cannot be reproduc		
Į	TOLERANCES ON		CHKD: DATE		a RADIAI	LL company _w	communicated to a third party wit vritten permission of RADIALL.	thout prior	
ļ	DECIMAL	ANGLE	D.N. 03/15,	/18	SSMC STRAIGHT MALE JACK				
			APVD: DATE	-	BULKHEAD/EDGE MOUNT				
			J.M. 03/15/	/18	FOR .032 BOARD				
Ī	REFERENCE:	•	MATERIALS & FINISHES:		SIZE	FSCM NO.	DWG NO.		REV
	ORIGINATED: C.E.		SEE NOTES		Α	19505	7029-1511-	-060	А
DATE: 03/15/18			SEE NOTES		SCALE 5:1		THIRD ANGLE PROJECTION	SHEET 1 OI	F 1