


THT Common Mode Chokes

PA3747.XXXNL



Dielectric Strength: 1500Vrms
Inductance Range: 0.67mH (at 5A) to 19.5mH (at 0.75A)
Height: 22.9mm Max
Footprint: 19.3mm x 18.2mm

Electrical Specifications @ 25°C - Operating Temperature -40°C to +125°C


Part Number	Inductance (1-2)=(3-4) (mH Min)	Current Rating ¹ (1-2)=(3-4) (A)	DCR (1-2)=(3-4) (mΩ Max)	Self Resonant Frequency (1-2)=(3-4) (MHz Min)	Impedance (kΩms Min at SRF)
PA3747.105NL	0.67	5.00	16	1.18	3.33
PA3747.205NL	1.28	4.00	25.5	1.10	5.04
PA3747.305NL	1.92	2.75	49.5	1.00	5.08
PA3747.405NL	2.68	2.25	71.5	0.94	11.57
PA3747.505NL	3.33	1.85	103.5	0.88	14.40
PA3747.605NL	4.06	1.55	132	0.78	17.93
PA3747.705NL	4.58	1.50	134	0.80	18.24
PA3747.905NL	6.03	1.45	154	0.30	24.38
PA3747.106NL	6.67	1.40	169	0.29	26.90
PA3747.146NL	9.10	1.00	207	0.21	42.69
PA3747.206NL	13.00	1.00	295	0.20	51.22
PA3747.306NL	19.50	0.75	572	0.12	80.65



- Notes:**
1. The current rating (I_{rated}) is based upon the temperature rise of the component and represents the rms current which will cause a typical temperature rise of 40 °C.
 2. The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range.

Mechanical

Schematic


PA3747.XXXNL





THT Common Mode Chokes

PA3747.XXXNL



For More Information

Americas - prodinfo_power_americas@yageo.com | **Europe** - prodinfo_power_emea@yageo.com | **Asia** - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.