
REVISIONS								
REV.	DESCRIPTION	DATE	APPROVED					
Α	INITIAL RELEASE	05/19/17	D.N.					





NOTES:

MATERIALS:

- 1. BODY = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
 2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

FINISHES:

- 1. BODY = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C, OVER 50 TO 100µin STRESS FREE NICKEL PER AMS-QQ-N-290.

 2. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N. CHKD:	DATE 05/19/17 DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior RADIALL company written permission of RADIALL.					6
DECIMAL ANGLE		P.H. APVD: J.M.	05/19/17 DATE 05/19/17	SMA STRAIGHT JACK TO STRIPLINE NON-CAPTIVE CONTACT					
REFERENCE: ORIGINATED: D.N.		MATERIALS & FINISHES: SEE NOTES		size A	FSCM NO. 19505	DWG NO. 9610—1	213	-003	rev A
DATE: 05/19/17					5:1	THIRD ANGLE PROJECTION	+ {}	SHEET 1 O	F 1