

June 2015

Multilayer Band Pass Filter (Balance Output Type) For 2402–2480MHz

DEA202450BT-7099A1

2.0x1.25mm [EIA 0805]*

* Dimensions Code JIS[EIA]



The products in this catalog will be or have been stopped production

Discontinue Issue Date	Jun. 3, 2022	
Last Purchase Order Date	Mar. 31, 2023	
Last Shipment Date	Mar. 31, 2024	

Please refer to our Web site about replacement information.





Multilayer Band Pass Filter (Balance Output Type) For 2402–2480MHz

Conformity to RoHS Directive

DEA202450BT-7099A1

SHAPES AND DIMENSIONS





Terminal functions

- 1 Unbalanced port
- 2 DC feed
- 3 N.C.
- 5 Balanced port
- 6 GND
- 7 Balanced port8 GND

Dimensions in mm


■ RECOMMENDED LAND PATTERN

0.35

Note1: Pin 2 of the filter provides a DC feed connection to the balanced ports. In the event that thisfunction is used, Pin 2 should be connected to ground using a de-coupling capacitor.

Note2: In the event that the pin 2 function is not used, the pin should be left unconnected.

EVALUATION BOARD



RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



DEA202450BT-7099A1

ELECTRICAL CHARACTERISTICS

Item	Frequency Range (MHz)	Min.	Тур.	Max.		
Unbalanced Port Characteristic Impedance (Ω)			50 (Nominal)			
Balanced Port Characteristic Impedance (Ω)			Matched to CSR BC04 IC			
Insertion Loss (dB)	2402 to 2480	_	_	3		
	880 to 960	35	_	_		
Attenuation (dB)	1710 to 1880	22	_	_		
Attenuation (ub)	1880 to 1910	20	_	_		
	4804 to 4960	18	_	_		
Return Loss at Unbalanced Port (dB)	2402 to 2480	8.5	- 0	_		
Return Loss at Balanced Port (dB)	2402 to 2480	8.5	—	_		
Phase Balance (deg.)	2402 to 2480	170	+	190		
Amplitude Balance (dB)	2402 to 2480	-2		2		

[•] Ta: +25±5°C

TEMPERATURE RANGE

Operating temperature	Storage temperature	
(°C)	(°C)	
-40 to +85	-40 to +85	


- All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.




DEA202450BT-7099A1

■ FREQUENCY CHARACTERISTICS


□SDS21 INSERTION LOSS




□SDS21 ATTENUATION




□SSS11 RETURN LOSS at UNBALANCE PORT




□SDD22 RETURN LOSS at BALANCE PORT



□PHASE BALANCE




□AMPLITUDE BALANCE



- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

■ RECOMMENDED REFLOW PROFILE



Preheating		Soldering				
		Critical zone (T3 to T4)		Peak		
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	Т3	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120s	sec 240 to 260°C	30sec max.

*t3: Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

- All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.