



Summary

[Request a quote](#)

[Catalog](#)

Triax	1
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Push-pull
Jacket cable outside diameter [mm]	2.30 - 3.20 mm
Matching parts	FFA.0S.650.CTAC32
Series	S - Indoor Stepped Insert

Technical details

Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Insert configuration value	0S.650 - 1 Triax (50 Ohm)
Insulator	T: PTFE
Rated current	6 Amps
Impedance	50 Ohm
VSWR	1.03 + 0.34 * f/GHz
Vtest	1200 V (AC), 1700 V (DC)
Contact Type	Triaxial 50 Ohm (Solder)
Cable type	RGT 178, RGT 174
Bucket Dia.	0.8
Contact Dia.	0.9 mm (0.035" in)

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pca-0s-650-ctlc32.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	PCA - Free receptacle, cable collet
Socket / Receptacle	Free
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	8.72 g


Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental protection	IP50
Minimal temperature	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	2.30 - 3.20 mm

Drawings



https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pca-0s-650-ctlc32.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	L	S2	C
mm.	8.9	33.5	6.5	4.2
in.	0.35	1.32	0.26	0.17

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/pca-0s-650-ctlc32.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.