



ELECTRONICS, INC.
 44 FARRAND STREET
 BLOOMFIELD, NJ 07003
 (973) 748-5089
<http://www.nteinc.com>



**NTE428
 Hardware
 Socket for 24-Lead DIP Type Package
 .100" (2.54mm) Lead Spacing**

Features:

- Dual Contacts Open Frame Structure
- Stackable End-to-End and Side-to-Side
- Polarization mark

Specifications:

Insulator	Thermoplastic
Contact	Phosphor Bronze, 150u" Tin Plating over 30u" to 50u" Nickel
Maximum Contact Resistance (Initial)	20mΩ
Minimum Insulation Resistance	1000MΩ
Dielectric Withstanding Voltage (Per Minute)	500V AC
Operating Temperature Range	-65° to +150°C
Storage Temperature Range	-20° to +80°C

