

# 75 ohm BNC plug to BNC jack DC Block inner from 10MHz to 3GHz rated 200 Volt in Stainless Steel



## **DC Blocks Technical Data Sheet**

**PE8261** 

#### **Features**

- Inner DC Blocks with Stainless Steel Body
- · BNC connectorized configuration

- Operates from 10 MHz to 3 GHz
- 75 Ohm Impedance

#### **Applications**

- Test & Measurement
- Ground Loop Elimination
- Signal to Noise Ratio (SNR) Improvement

### Description

Pasternack's PE8261 is an inner DC block with BNC connectors. It has a blocking capacitor on the inner conductor and operates from 10 MHz to 3 GHz. Our BNC DC block offers good insertion loss of 0.5 dB and has a maximum operating voltage of 200 Vdc. DC blocks are commonly used to filter out unwanted DC signals, while allowing AC drive signals to pass through. They can help improve signal to noise ratio (SNR), eliminate ground loops, or provide isolation in your test setup. All of Pasternack's DC blocks are in stock and available to ship same-day.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.01		3	GHz
Impedance		75		Ohms
VSWR			1.3:1	
Insertion Loss			0.5	dB
Operating Voltage (DC)			200	Volts

#### **Mechanical Specifications**

Size

 Length
 2.09 in [53.09 mm]

 Width
 0.571 in [14.5 mm]

 Height
 0.571 in [14.5 mm]

 Weight
 0.05 lbs [22.68 g]

Housing Material and Plating Passivated Stainless Steel

#### Configuration

Package Type Connectorized

Description	Connector 1	Connector 2
Туре	BNC Male	BNC Female
Inner Conductor Material and Plating	Brass, Gold	Bronze, Gold

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 75 ohm BNC plug to BNC jack DC Block inner from 10MHz to 3GHz rated 200 Volt in Stainless Steel PE8261

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



# 75 ohm BNC plug to BNC jack DC Block inner from 10MHz to 3GHz rated 200 Volt in Stainless Steel



### **DC Blocks Technical Data Sheet**

PE8261

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

75 ohm BNC plug to BNC jack DC Block inner from 10MHz to 3GHz rated 200 Volt in Stainless Steel from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 75 ohm BNC plug to BNC jack DC Block inner from 10MHz to 3GHz rated 200 Volt in Stainless Steel PE8261

URL: https://www.pasternack.com/75-ohm-bnc-dc-block-10-mhz-3-ghz-pe8261-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

**PE8261 CAD Drawing**75 ohm BNC plug to BNC jack DC Block inner from 10MHz to 3GHz rated 200 Volt in Stainless Steel

