




SCREW ON STRAIGHT MALE JACK CRIMP TYPE SLIDE TYPE - CABLE 2.6/50S



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	BBR
Center contact	BRASS	NPGR
Outer contact		
Insulator	PTFE	
Gasket		
Others parts	BRASS	BBR
-	-	-
-	-	-



Technical Data Sheet

SCREW ON STRAIGHT MALE JACK CRIMP TYPE SLIDE TYPE - CABLE 2.6/50S

PAGE 2/2	ISSUE 19-03-15A	SERIES SMP-MAX	PART NUMBER R222M20710
-----------------	------------------------	----------------	------------------------

PACKAGING

Standard	Unit	Other
100	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

Impedance			50	Ω
Frequency			0-6	GHz
VSWR	1.25*	+	0.0000	x F(GHz) Maxi
Insertion loss			0.15*	√F(GHz) dB Maxi
RF leakage	- (NA	- F(GHz)) dB Maxi
Voltage rating	,		335	Veff Maxi
Dielectric withstanding volta	ge		750	Veff mini
Insulation resistance			5000	$M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End NA N mini Axial force - Opposite end NA N mini N.cm mini Torque NA

Recommended torque

Mating NA N.cm Panel nut 100 N.cm Clamp nut N.cm NA A/F clamp nut 0.0000 mm

Mating life 100 Cycles mini g

Weight 3.1700

ENVIRONMENTAL

Operating temperature -55/+165 °C Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	2	5	8.5	0	6.5	0

Assembly instruction: Crimp 01

Recommended cable(s)

RG 174 RG 316 KX 22A ECO 316

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off 53 N mini - torque NA N.cm

TOOLING

Part Number	Description	Hexagon
R282211000	CRIMPING TOOL	3.25
R282235003	CRIMPING DIES M22520/5-03	3.25
R282293000	CRIMPING TOOL M22520/5-01	

OTHER CHARACTERISTICS

*Coaxial Transmission Line Only *Slide type connector+Bullet+Snap type receptacle Radial working angle: 3°min Axial working range: 2mm

Because of the BBR plating, the typical values of the outer contact resistance may slightly differ compared to the NPGR plated jacks.