

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY					
REV	DESCRIPTION	DATE	APPROVED		
-	NRN 44864	05/20	STW		





MATERIAL:

BODY, FERRULE, & CONTACT:

BERYLLIUM COPPER

INSULATOR:

PTFE

FINISH:

BODY, CONTACT & FERRULE:

GOLD OVER COPPER

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 40.0 GHz.

MATERIAL: SEE NOTES					
FINISH: SEE NOTES					
SURFACE AREA: N/A					
PROPRIETARY					
THE INFORMATION CONTAINED IN THIS DRAWIN IS THE SOLE PROPERTY OF SV MICROWAVE, IN ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.					

RIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANG		
H:	SEE NOTES	DECIMAL: .X ±.030 .XX ±.010		
ACE AREA: N/A		.XXX $\pm .005$ INTERPRET DIMENSIONS AND TOLERAN		
PROPRIETARY NFORMATION CONTAINED IN THIS DRAWING E SOLE PROPERTY OF SV MICRO AVAILABLE OF THE PROPERTY OF SV MICRO AVAILABLE OF THE PROPERTY OF SV MICRO AVAILABLE OF THE PROPERTY OF THE PRO		PER ASME Y14.5M - 1994		
		THIRD ANGLE PROJECTION		

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: X ±.030	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES ,005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN 005 T.I.R. 7) REMOVE ALL BURRS		MICROWAVE www.svmicrowave.com		
.XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994			SMPM JACK (NON-MAGNETIC)		
THIRD ANGLE PROJECTION	DRAWN:	SJ 05/27/20	FOR .085 CABLE		
	CHECKED:	STW 05/27/20	SIZE DWG. NO.	3221-4	0132
	APPROVED:	STW 05/27/20	SCALE: 16:1		SHEET 1 OF 1