
**Technical Data Sheet** 

TNC ATTENUATOR 15 DB 3 GHZ 1W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

## **Technical Data Sheet**

TNC ATTENUATOR 15 DB 3 GHZ 1W



GE <b>2/2</b>	ISSUE	01-04-20B	SERII ATTENU			PAR	T NUMBER	R412515124
			1			RACTERISTICS		
<b>F</b> re		1-)	DC - 2			]		
	Frequency (GHz) V.S.W.R (≤)		1.2		2 - 3 1.3			
	/iation(±dB)		0.70		0.70			
		I		I		1		
Ope	erating Freq	uency Rang	e			DC - 3		GHz
Imp	Impedance Nominal Attenuation		1			50	50	Ω
					15			dB
	Peak power at 25°C (1µs, 1‰) Average power at 25°C			100 1				W
Ave								W (Free Air Cooled)
								W (Conduction Cooled)
Wei	ght		16,77	g				
			EN erating tempe	VIRONI	ange		0/+85 °C	]
			EN	IVIRONI erature ra	er derating Vo	-4		
			En erating tempera rage tempera (%) 50 10 10 10 10	Pow	er derating Vo	-44 ersus temperature	0/+85 °C 0/+85 °C	
			En erating tempera rage tempera (%) 50 10 10 10 10	Pow	er derating Vo	-44 ersus temperature	0/+85 °C 0/+85 °C	

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.