






STRAIGHT PLUG FULL CRIMP CABLE 2.6/50 S

PAGE 1/2 ISSUE 15-05-15G SERIES QMA PART NUMBER R123071000









All dimensions are in mm.



| COMPONENTS | MATERIALS | PLATING (μm) | |
|-------------------------|----------------|--------------|--|
| Body Center contact | BRASS BRASS | BBR NPGR | |
| Outer contact Insulator | BRONZE PTFE | BBR | |
| Gasket | - | | |
| Others parts | BRASS | BBR | |
| - | - | - | |
| - | - | - | |



Technical Data Sheet

STRAIGHT PLUG FULL CRIMP CABLE 2.6/50 S

PAGE 2/2 ISSUE 15-05-15G SERIES QMA PART NUMBER R123071000

PACKAGING

| 100 | Contact us | Contact us |
|----------|------------|------------|
| Standard | Unit | Other |

ELECTRICAL CHARACTERISTICS

Impedance 50 Frequency GHz 0-6 **VSWR** 0.0000 x F(GHz) Maxi Insertion loss .05 √F(GHz) dB Maxi RF leakage 80 - F(GHz)) dB Maxi - (Veff Maxi Voltage rating 250 Dielectric withstanding voltage 750 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force – Mating End
Axial force – Opposite end
Torque

18 N mini
N mini
N mini
N n.cm mini

Recommended torque

 Mating
 NA
 N.cm

 Panel nut
 NA
 N.cm

 Clamp nut
 NA
 N.cm

 A/F clamp nut
 0.0000
 mm

Mating life 100 Cycles mini

Weight **5.7550** g

ENVIRONMENTAL

Operating temperature -40/+105 °C
Hermetic seal NA Atm.cm3/s
Panel leakage NA

SPECIFICATION

CABLE ASSEMBLY

| Stripping | а | b | С | d | е | f |
|-----------|---|-----|------|---|-----|---|
| mm | 3 | 6.3 | 10.8 | 0 | 7.8 | 0 |

Assembly instruction: Crimp 02

Recommended cable(s)

RG 188 RG 316 KX 22A

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

 - pull off
 90
 N mini

 - torque
 NA
 N.cm

TOOLING

| Part Number | Description | Hexagon | |
|-------------|------------------------------|---------------|--|
| R282211000 | CRIMPING TOOL | 3.25 | |
| R282235003 | CRIMPING DIES M22520/5-03 | 3.25 | |
| R282281000 | CRIMPING TOOL | 2x4 (pos. 5) | |
| R282293000 | CRIMPING TOOL M22520/5-01 | | |
| R282967015 | POSITIONER FOR CRIMPIMG TOOL | | |
| R299511016 | STRIPPING CASETTE .059/.248 | denudage B, E | |

OTHER CHARACTERISTICS

VSWR: 1.12 max from 0 to 3GHz Intermod.: -120 dBc at 1.8GHz (2x20W) RF leakage(interf.): 3<F<6GHz: >70dB