





SMA ATTENUATOR 15 DB 18 GHZ 2W

PAGE 1/2 ISSUE 17-02-16D SERIES ATTENUATOR PART NUMBER R411815121





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 2 OVER NICKEL 2	
Female center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2	
Outer contact	-	-	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINA		
Resistor	THIN FILM		
Others parts	-	-	





SMA ATTENUATOR 15 DB 18 GHZ 2W

PAGE <b>2/2</b>	ISSUE 17-02-16D	SERIES ATTENUATOR	PART NUMBER <b>R411815121</b>
-----------------	-----------------	----------------------	-------------------------------

## **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4	12.4 - 18
V.S.W.R (≤)	1.15	1.20	1.25	1.35
Deviation(±dB)	0.50	0.50	0.60	1.00

Operating Frequency Range	DC - 18	GHz
Impedance	50	Ω
Nominal Attenuation	15	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


### MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	<b>4,3600</b> g		

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	<b>-55 /+125</b> °C
Storage temperature range	-55 /+125 °C

#### Power derating Versus temperature



## SPECIFICATION

# OTHER CHARACTERISTICS