

	905
	0
	\mathcal{O}
_	9
M	95
	\rightarrow
	\mathcal{S}
	000
	\bigcirc
_	\bigcirc



REVISIONS									
REV.	DESCRIPTION	DATE	APPROVED						
А	INITIAL RELEASE	02/10/16	D.N.						



NOTES:

MATERIALS:

- 1. BODY & COUPLING NUT = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
 2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 3. CONTACT & RETAINING RING = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
 4. GASKET = SILICONE RUBBER PER ZZ-R-765, CLASS 2B, GRADE 65-75.
 5. EMI GASKET = CONDUCTIVE SILVER/SILCONE ELASTOMERS 70 DUROMETER.

FINISHES:

- 1. BODY & COUPLING NUT = PASSIVATE PER SAE-AMS-2700 2. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON DECIMAL ANGLE		D.N. CHKD:	DATE 02/10/16 DATE	communicated to a third party without prior a RADIALL companywritten permission of RADIALL.				
İ			N.D.	02/10/16					
			APVD:	DATE	(4) HOLE FLANGE MOUNT				
			J.M.	02/10/16					
ſ	REFERENCE:	•	MATERIALS & FI	NISHES:	SIZE	FSCM NO.	DWG NO.		REV
	ORIGINATED: D.N.		SEE NOTES		Α	19505	9051-9513	-000	А
	DATE: 02/10/16				SCALE 4:1		THIRD ANGLE PROJECTION	SHEET 1 O	F 1