





SCREW-ON MALE RECEPTACLE HERMETIC-WITH CYLINDRICAL CONTACT

PAGE 1/3 ISSUE 08-02-16B SERIES BMA PART NUMBER R128639020







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	STAINLESS STEEL	GOLD 0.5 OVER NICKEL 2
Center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2
Outer contact	-	-
Insulator	PTFE	
Gasket	A-G4MC	
Others parts	_	-
-	-	-
-	-	-



Technical Data Sheet

SCREW-ON MALE RECEPTACLE HERMETIC-WITH CYLINDRICAL CONTACT

PAGE 2/3	ISSUE 08-02-16B	SERIES BMA	PART NUMBER R128639020
PAGE 2 / 3	ISSUE 08-02-16B	SERIES BMA	PART NUMBER R128639020

PACKAGING

Standard	Unit	Other
1	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

 $\begin{array}{cccc} \text{Impedance} & & \textbf{50} & \Omega \\ \text{Frequency} & & \textbf{0-22} & \text{GHz} \\ \end{array}$

x F(GHz) Maxi √F(GHz) dB Maxi VSWR 1.04 0,0090 Insertion loss 0.03 - F(GHz)) dB Maxi RF leakage NA - (Voltage rating 500 Veff Maxi Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

 Axial force - Mating End
 27
 N mini

 Axial force - Opposite end
 27
 N mini

 Torque
 NA
 N.cm mini

Recommended torque

 Mating
 NA
 N.cm

 Panel nut
 280
 N.cm

Mating life 1000 Cycles mini Weight 1,2320 g

ENVIRONMENTAL

Operating temperature -65/+125 °C
Hermetic seal 10-8 Atm.cm3/s
Panel leakage NA

SPECIFICATION

OTHER CHARACTERISTICS

Assembly instruction:NA

Others:

-




Technical Data Sheet


SCREW-ON MALE RECEPTACLE HERMETIC-WITH CYLINDRICAL CONTACT


PAGE 3/3 ISSUE **08-02-16B** SERIES **BMA** PART NUMBER **R128639020**

PANEL DRILLING



MOUNTING HOLE DETAIL





Assemble metal gasket onto connector. Screw both parts into the housing. Tighten the connector up to 280 Ncm torque (use special tooling set RADIALL R282 340). Thus the connection hermeticity is guaranteed at 1 . 10-8 atm.cm³/sec. Then solder the pin.

Be careful not put too much solder.