





50W 0.9-2.1GHZ 10DB DIRECTIONAL COUPLER

PAGE 1/2	ISSUE 05-12-19A	SERIES COUPLER	PART NUMBER <b>R433463000</b>
----------	-----------------	-------------------	-------------------------------

**Scale 3:4** 





All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **166,5200** g







50W 0.9-2.1GHZ 10DB DIRECTIONAL COUPLER

PAGE <b>2</b> / <b>2</b>	ISSUE <b>05-12-19A</b>	SERIES COUPLER	PART NUMBER <b>R433463000</b>
--------------------------	------------------------	-------------------	-------------------------------

## **ELECTRICAL CHARACTERISTICS**

Frequency operating range:	0.9 – 2.1 GHz
Impedance:	50 Ω
VSWR: - Main Line	1.20 max.
- Coupled Line	1.20 max.
Nominal Coupling:	10 dB
Coupling Precision:	± 0.5 dB
Insertion Loss:	1 dB max.
Directivity:	22 dB mini
Frequency Sensitivity:	± 0.3 dB
Average Power at 25°C	50W
Peak Power at 25°C	3000W

## **MECHANICAL CHARACTERISTICS**

Connector type:	N female per MIL-C 39012
Coaxial Termination :	SMA, 50 Ω, 1W

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature :	-25°C / +85°C
Storage temperature :	-40°C / +100°C