

DC to 40GHz 20dB Resistive Coupler

FPC07803



DESCRIPTION

DLI introduces its new high frequency surface mountable catalog resistive couplers. These couplers incorporate DLI's high dielectric ceramic materials which provide small size and minimal performance variation over temperature. The components are well matched for monitoring incident and reflected power.

FEATURES


- Small Size
- Excellent Repeatability
- Surface Mountable
- Moisture Sensitivity Level: MSL1
- Frequency Stable over Temperature
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω

SPECIFICATIONS*

Parameter	Frequency (GHz)	Min	Max
Passband Insertion Loss* (dB)	DC-40	2.5	3
Passband Return Loss (dB)		10	
Coupling (dB)		20	±3
Input Power (W)			TBD
Size (LxWxH)	0.060 x 0.088 x 0.010 inch (1.52 x 2.24 x 0.254mm)		

^{*}Electrical specifications based on typical mounted performance at room temperature. Insertion loss shall vary $\pm 0.5 dB$ over temperature.

Typical Measured Performance



^{*}Typical measured performance mounted on RO4350B test board at 25°C.

2777 Route 20 East, Cazenovia, NY 13035| Ph: (315)655-8710 | KCCSales@knowles.com





knowles compex · dli · Johanson mfg novagap · syfer · voltronics

www.knowlescapacitors.com

DC to 40GHz 20dB Resistive Coupler

FPC07803







Physical Dimensions

0.060 7803 I

Side



Recommended PCB Layout



- 50Ω trace dimensions are application specific.
- Ensure adequate grounding beneath the part.
- Trace feed locations can be horizontal, vertical, or angled.







2777 Route 20 East, Cazenovia, NY 13035| Ph: (315)655-8710 | KCCSales@knowles.com