



Electrical Specifications

Notch Center Frequency: 915 MHz
Notch Band: 902-928 MHz
Notch Band Attenuation: >20 dB
Low Side of Passband: 500-850 MHz
High Side of Passband: 970-1200 MHz
Insertion Loss in Passband: <1 dB
Return Loss in Passband: >15 dB
Rejection: >20dB @ 902-928 MHz
Power Handling: 20 Watts Max


Mechanical

Connector Type: SMA (M/F)
Dimensions: 2.50 x 1.125 x 0.75 Inches

Environmental

Operating Temperature: 0 to +60° C
Storage Temperature: -40 to +85° C
Shock: 10 G. 11 ms
Vibration: 10 G. 5 to 200 Hz

Outline Drawing:



DS-NS2095-10152015-Rev1



Response Plot:

