




80W 2-4GHZ 10DB DIRECTIONAL COUPLER

PAGE 1/2 ISSUE 27-01-20S SERIES COUPLER PART NUMBER R432533000

Scale 2:1



All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **21,52** g







80W 2-4GHZ 10DB DIRECTIONAL COUPLER

PAGE 2 / 2	ISSUE 27-01-20S	SERIES COUPLER	PART NUMBER R432533000
--------------------------	------------------------	-------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency operating range:	2 – 4 GHz
Impedance:	50 Ω
VSWR: - Main Line	1.15 max.
- Coupled Line	1.15 max.
Nominal Coupling :	10 dB
Coupling Precision:	± 0.3 dB
Insertion Loss:	1 dB max.
Directivity:	20 dB mini
Frequency Sensitivity:	± 0.8 dB
Average Power at 25°C	80W
Peak Power at 25°C	3000W

MECHANICAL CHARACTERISTICS

Connector type:	SMA female per MIL-C 39012
Coaxial Termination:	SMA, 50 Ω, 1W

ENVIRONMENTAL CHARACTERISTICS

Operating temperature :	-25°C / +70°C
Storage temperature :	-25°C / +70°C