# **Technical Data Sheet**



SP6T Ramses SMA 18GHz Latching Self-cut-off Auto-reset Indicators 12Vdc BCD TTL Diodes D-sub connector

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573492685

### RF CHARACTERISTICS

Number of ways : 6

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

## **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 960 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V)

Terminals : 25 pins D-SUB male connector

BCD inputs (E) - High level : 3.5 to 5.5 V / 800μA at 5.5 V - Low level : 0 to 1.5 V / 20μA at 0.8 V

### MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012
Life : 5 million cycles per position

Switching Time\*\*\* : < 40 msConstruction : Splashproof
Weight : < 220 g

# **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)









SP6T Ramses SMA 18GHz Latching Self-cut-off Auto-reset Indicators 12Vdc BCD TTL Diodes D-sub connector


PAGE **2/2** ISSUE **22-03-22** SERIE: SPnT PART NUMBER: **R573492685** 

### **DRAWING**




	BCD TRUTH TABLE					
E3	E2	E1	RF continuity	Ind.		
0	0	0	All ports open (Forced Reset)	1		
0	0	1	IN ↔ 1	D.E		
0	1	0	$IN \leftrightarrow 2$	D.F		
0	1	1	$IN \leftrightarrow 3$	D.G		
1	0	0	$IN \leftrightarrow 4$	D.H		
1	0	1	$IN \leftrightarrow 5$	D.I		
1	1	0	IN ↔ 6	D.J		





General tolerances: ±0,5 mm [0,02 in]

# **SCHEMATIC DIAGRAM**



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.