



**Electrical specifications**

**Center Frequency:** 2725 MHz  
**Frequency Range:** 2715-2735 MHz  
**Bandwidth:** 20MHz  
**Insertion Loss:** ≤3.0 dB  
**Return Loss:** ≥14dB  
**Rejection1:** 50dB Min. @2690MHz  
**Rejection2:** 50dB Min. @2760MHz


**Mechanical**

**Mounting Method:** Threaded holes  
**Connectors:** N-Type (f)  
**Dimensions:** 4.69 x 3.19 x 1.18 in

**Environmental**

**Operating Temperature:** -40 to +85 deg.C  
**Storage Temperature:** -55 to +95 deg.C  
**Shock:** 20 G. 11ms  
**Vibration:** 20 G. 5 to 200 Hz

**Outline Drawing:**



2 decimal places: +/-0.01 inches [+/-0.3mm]  
 3 decimal places: +/-0.005 inches [+/-0.13mm]  
 Angles: +/-1 Deg.

When max dimensions are called out the above tolerances do not apply as long as it is under the max call out.

DS-B11625-04192019-Rev0