



- Specification:**
- Electrical Char  
Insulation Resistance: 500MΩ min. 500V DC for 1 minute  
Contact Resistance: 30mΩ max.  
Rating Current: 1.5A max.  
Rating Voltage: 150V AC  
Dielectric Voltage: 1000 Vrms at 1MA 60 sec. min.
  - Physical Char  
Housing: PBT Glass filled (UL 94V-0) Color: Black  
Soldering Temperature: 235°C for 5 sec.  
Spring Wire: 0.45mm Dia Phosphor Bronze  
6u" Gold plating over Nickel  
Temperature Range: -40°C to +85°C  
Durability: 750 mating cycles min.
  - Packing: Tray

**RoHS compliant**  
Unit:mm

Scale	Free	Angle	+0°30'	Id.	Modification	Date	Name
TOLERANCE							
.XX	±0.20					28.10.2015	Amy
.XXX	±0.13						
.XXXX	±0.05						
DIM	TOL						

Date	Name	Customer-No.	Drawing-No.	Replace	SHEET
28.10.2015	Amy				
28.10.2015	Amy				
		ASSMANN WSW-No.	A-2014-2-4-LP/FSS-R	ASS 7045 CO	rev00



1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	B
1	2	3	4	5	6	7	C
1	2	3	4	5	6	7	D
1	2	3	4	5	6	7	E
1	2	3	4	5	6	7	F
1	2	3	4	5	6	7	G
1	2	3	4	5	6	7	H