



Electrical specifications

Center Frequency: 922-948 MHz
Insertion loss: 1.5 dB
Return loss: 15 dB
Rejection 1: >=55 dB@897.5 MHz
Rejection 2: >=55 dB@972.5 MHz
Impedance: 50 Ohms In/Out
Power Handling: 50 W CW


Mechanical

Mounting Method: Threaded Mounting Holes
Connector Type: N Female
Dimensions: 120 X 60 X 48 mm

Environmental

Operating Temperature: -45 to +85° C
Storage Temperature: -55 to +95° C
Shock: 20 G. 11ms
Vibration: 20 G. 5 to 200 Hz

Outline Drawing:



NOTES

1. BLACK PAINTING AFTER SILVER PLATING
2. UNLESS OTHER SPECIFIED, THE TOLERANCE IS ±0.1

DS-B903-03152018-Rev0



Plot:

