



**ANATECH ELECTRONICS INC**  
RF & Microwave Filters & Products

# 1250 MHz Suspended Stripline High Pass Filter

**Part Number: AE1250SSH6582**



## Electrical Specifications

**Cut Off Frequency:** 1.25GHz  
**Pass Band Frequency:** 1.25~12GHz  
**Pass Band Insertion Loss:**  
 $\leq 1.5\text{dB @ } 1.25\sim 1.35\text{GHz}$   
 $\leq 1.0\text{dB @ } 1.35\sim 12\text{GHz}$   
**Pass Band VSWR:**  $\leq 1.5:1$   
**Stop Band Attenuation:**  $\geq 50\text{dB @ DC}\sim 0.98\text{GHz}$   
**Impedance:** 50 Ohms  
**Power Handling:**  $\leq 15\text{W}$


## Mechanical

**Mounting Method:** Through Holes  
**Connector Type:** SMA-Female  
**Dimensions:** 52.0 x 20.5 x 10.0 mm

## Environmental

**Operating Temperature:**  $-45^\circ$  to  $+85^\circ$  C  
**Storage Temperature:**  $-55^\circ$  to  $+95^\circ$  C  
**Shock:** 20 G. 11ms  
**Vibration:** 20 G. 5 to 200 Hz

## Outline Drawing:



Tolerance:  $\pm 0.01$  inches [ $\pm 0.3\text{mm}$ ]  
 Angles:  $\pm 1$  Deg.

DS-SSH6582-01252019-Rev0

\*Tolerance as shown unless otherwise specified in the datasheet electrical specification tables above.

\*When max dimensions are called out the above tolerances do not apply as long as it is under the max call out.

70 Outwater Lane Phone: (973) 772-4242  
 Garfield, NJ 07026 Fax : (973) 321-3941

Email: [sales@anatechelectronics.com](mailto:sales@anatechelectronics.com)  
 Web: [www.anatechelectronics.com](http://www.anatechelectronics.com)



**Response Plot:**

