

Double-Balanced Mixer 8 to 43 GHz

Rev. V1

Features

Low Conversion Loss: 8 dBHigh Linearity: 22 dBm IIP3

• Wide IF Bandwidth: DC to 10 GHz

High Isolation

• Die Size: $1.20 \times 0.97 \times 0.10 \text{ mm}$

RoHS* Compliant

Description

MAMX-011036-DIE is a double-balanced passive diode mixer MMIC. The mixer offers low conversion loss, high linearity and a wide IF bandwidth. The double-balanced circuit configuration provides excellent port isolation while internal 50-ohm matching simplifies its application.

This mixer is well suited for applications such as test and measurement, microwave radio and radar.


MAMX-011036-DIE is also available in a 3 mm QFN package. Refer to datasheet MAMX-011036.

Ordering Information

Part Number	Package	
MAMX-011036-DIE	Vacuum Release Gel Pack ¹	
MAMX-011036-SB2	Sample Board	

1. Die quantity varies.

Functional Schematic



Bond-pad Configuration

Pad No.	d No. Function Pad No.		Function	
1	GND ²	6	GND ²	
2	LO	7	GND ²	
3	GND ²	8	RF	
4	GND ²	9	GND ²	
5	IF	10	GND ³	

- 2. These pads are internally connected to ground, and they can be left unconnected.
- 3. The backside of the die must be connected to RF, DC and thermal ground.

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.

^{*} Restrictions on Hazardous Substances, European Union Directive 2011/65/EU.



Double-Balanced Mixer 8 to 43 GHz

Rev. V1

Electrical Specifications⁴: $F_{IF} = 500 \text{ MHz}$, $P_{LO} = +15 \text{ dBm}$, $T_A = 25^{\circ}\text{C}$, $Z_0 = 50 \Omega$

Parameter	Test Conditions	Units	Min.	Тур.	Max.
LO and RF Frequency	_	GHz	8	_	43
IF Frequency	_	GHz	0	_	10
LO Power	_	dBm	_	15	_
Conversion Loss	8 - 20 GHz 20 - 34 GHz 34 - 43 GHz	dB -		8 8 9	10 11 13
Input P1dB	— dBm		_	13	_
Input IP3	P_{RF} = -10 dBm/tone, Δf = 1 MHz dBm		_	22	_
Input IP2	P _{RF} = -10 dBm/tone, Δf = 1 MHz	dBm	_	45	_
LO-to-RF Isolation	_	dB	_	40	_
LO-to-IF Isolation	8 - 20 GHz 20 - 34 GHz 34 - 43 GHz	GHz dB		40 33 50	_
RF-to-IF Isolation	8 - 20 GHz 20 - 34 GHz 34 - 43 GHz	4 GHz dB		9 25 38	_
RF Return Loss	RF = 15 GHz	dB	_	5	_
IF Return Loss	IF = 500 MHz	dB	_	15	_

^{4.} All specifications refer to down-conversion operation, unless otherwise noted.

Absolute Maximum Ratings^{5,6}

Parameter	Absolute Maximum	
LO Power	23 dBm	
RF or IF Power	20 dBm	
Junction Temperature ⁷	+150°C	
Operating Temperature	-55°C to +85°C	
Storage Temperature	-65°C to +150°C	

^{5.} Exceeding any one or combination of these limits may cause permanent damage to this device.

Handling Procedures

Please observe the following precautions to avoid damage:

Static Sensitivity

These electronic devices are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these HBM Class 1B devices.

2

MACOM does not recommend sustained operation near these survivability limits.

^{7.} Operating at nominal conditions with $T_J \le +150^{\circ}C$ will ensure MTTF > 1 x 10^6 hours.




Double-Balanced Mixer 8 to 43 GHz


Rev. V1

Typical Performance Curves, P_{LO} = +15 dBm, T_A = 25°C


IF Bandwidth & Return Loss



Isolation



RF Return Loss






Double-Balanced Mixer 8 to 43 GHz


Rev. V1

Typical Performance Curves vs. LO Power, T_A = 25°C


Conversion Gain




Input P1dB




Input IP3 at P_{LO} = +15 dBm



Input IP2 at P_{LO} = +15 dBm



Up Conversion Gain



All performance curves refer to down-conversion operation, unless otherwise noted. $% \label{eq:conversion}$

Two-tone input power = -10 dBm each tone, 1 MHz spacing.

4

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit www.macom.com for additional data sheets and product information.




Double-Balanced Mixer 8 to 43 GHz


Rev. V1

Typical Performance Curves vs. Temperature, P_{LO} = +15 dBm


Conversion Gain



Input IP3



Input IP2



All performance curves refer to down-conversion operation, unless otherwise noted. $% \label{eq:conversion}$

Two-tone input power = -10 dBm each tone, 1 MHz spacing.



Double-Balanced Mixer 8 to 43 GHz


Rev. V1

MxN Spurious Rejection @ IF Port (dBc IF)

RF = 17.5 GHz @ -10 dBm LO = 18.0 GHz @ +15 dBm

	NxLO				
MxRF	0	1	2	3	4
0	x	11	40	х	x
1	2	0	28	42	х
2	77	65	52	65	80
3	х	90	73	76	77
4	х	х	95	104	104

Assembly Guideline



Notes:


Attach bare die to PCB or carrier using conductive epoxy. Bond die signal pads to PCB 50 Ω traces using 1.0 mil gold wire. Two bond wires are recommended on each signal pad for optimal performance. There is no need to bond the die GND pads.



Double-Balanced Mixer 8 to 43 GHz

Rev. V1

Outline Drawing



Notes:

Units are in microns with a tolerance of $\pm 5~\mu m$, except for die exterior dimensions which are street-center-to-street-center – nominal kerf, $\pm 20~\mu m$ tolerance.

Die thickness is 100 ±10 µm.

RF, LO and IF Bond-pads are 160 x 100 $\mu m.$



Double-Balanced Mixer 8 to 43 GHz

Rev. V1

MACOM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with MACOM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.